

6ft (2m) Micro HDMI to DVI Cable - Micro HDMI to DVI Adapter Cable - Micro HDMI Type-D Device to DVI-D Single Link Monitor/Display/Projector Video Converter Cord - Durable

Produkt ID: HDDDVIIMM2M



The HDDDVIIMM2M 2m Micro HDMI® to DVI-D Cable enables you to view your presentations, videos and pictures saved on your HDMI Micro-equipped mobile devices (Tablet, Smartphone) on a DVI-D capable display or projector. As an option, in order to incorporate audio with your video presentations you can use our 6ft (2m) Slim 3.5mm Stereo Audio Cable (MU6MMS).

Backed by Lifetime Warranty, the HDDDVIIMM2M is designed and constructed for maximum durability, to ensure dependable performance.

Certifikat, rapporter och kompatibilitet



Användning

- Connect your HDMI Micro-equipped mobile device (Smartphone, Tablet, etc.) to a DVI-D display or projector

Funktioner

- MICRO HDMI TO DVI CABLE: 6.6ft (2m) Micro HDMI male to DVI-D (24-pin) male cable supports Full

HD 1920x1200p, 60Hz/1080p video, Single link, 3.9 Gbps bandwidth, 24 Bpp (RGB) color depth

- **DURABLE:** Full HD high speed fully molded video adapter cable with durable PVC jacket for high strength and reliability; Flexible PVC strain relief prevents fraying or damage due to repetitive bending or rough usage; Ideal for Commercial environments
- **QUALITY CONSTRUCTION:** Micro HDMI to DVI converter cable constructed with 30AWG wire, gold-plated connectors, and superior EMI shielding with Al-Mylar foil and copper braid improve signal integrity and reliability, providing higher quality video and audio
- **APPLICATIONS:** This cord connects Micro HDMI (Type-D) devices: GoPro Hero/Raspberry Pi 4/cameras (DSLR/Video)/Nikon/Canon EOS to your DVI-Digital monitor/DVI display/projector; Ideal for viewing on larger screens; works w/ Samsung/Dell/HP/Acer/LG monitors
- **SPECS:** 6.6 feet (2 meter) | Black | HDMI Male (Type-D/Micro) to DVI-Digital (24-pin) Female | Gold-plated connectors | 30 AWG | 0.2" (5mm) OD | PVC Jacket | EMI Shield: Al-Mylar foil with 85% Copper Braid | Lifetime Warranty

Hårdvara

Garantipolicy	Lifetime
Active or Passive Adapter	Passiv
Kontaktplätering	Guld
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med flätning

Kontakt(er)

Connector A	1 - Micro HDMI (19-stifts)
Connector B	1 - DVI-D (19-stifts)

Utseende

Färg	Svart
Kontakttyp	Rak
Tråddimension	30 AWG
Kabellängd	6.6 ft [2 m]
Produktlängd	6.6 ft [2.0 m]
Produktbredd	1.6 in [4.0 cm]

Produkthöjd	0.6 in [1.6 cm]
Produktvikt	3.7 oz [106.0 g]

Förpackning

Förpackningsantal	1
Paketets längd	6.3 in [16.0 cm]
Paketets bredd	7.8 in [19.7 cm]
Paketets höjd	0.9 in [2.3 cm]
Fraktvikt (förpackning)	4.0 oz [114.0 g]

Vad det är i lådan

Ingår i paketet	1 - 2m Micro HDMI® to DVI-D Cable - M/M
-----------------	---

Warranty Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.