

8in (20cm) HDMI to DVI Adapter, DVI-D to HDMI (1920x1200p), 10 Pack, HDMI Male to 24 Pin DVI-D Female, Digital Monitor Adapter Cable M/F, HDMI to DVI Display Cord, Black

Produkt-ID: HDDVIMF8IN10PK



Need to connect your HDMI® equipped device to a DVI-D digital display? This 10 pack 8in HDMI to DVI adapter provides the perfect solution.

Connect your HDMI capable source to a DVI digital monitor, TV or projector, and share your presentations, pictures and videos. Simply plug any one of our male-to-male DVI-D cables, such as our 3ft DVI-D single-link cable 3ft DVI-D single-link cable (DVIMM3) into the adapter and connect the adapter to your device.

Perfect for use in a boardroom, your home office or when travelling for work, you can be ready to connect wherever you are.

Need a way to incorporate audio into your presentation? You can use our 1m 3.5mm audio cable 1m 3.5mm audio cable (MU3MMS).

Reduce stress and prevent damage on the device port. The 8-inch cable design reduces the strain on the port as well as the connectors, plus it doesn't block other open ports, leaving them open for connecting other devices.

The adapter fits nicely inside your laptop bag, purse, backpack or other carrying case, making it the perfect mobile accessory to keep in your carry-on baggage. Arrive prepared when presenting to a potential client, teaching offsite, or travelling to a customer location.

The HDDVIMF8IN10PK HDMI to DVI adapter is backed by StarTech.com® lifetime warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

Hardware

Garantiebestimmungen	Lifetime
Active or Passive Adapter	Passiv
Steckverbinderplatten	Gold
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Typ der Kabelabschirmung	Aluminium-Mylar-Folie mit Geflecht

Leistung

Max. Digitalauflösungen	1920x1200
-------------------------	-----------

Steckverbinder

Steckverbinder A	1 - HDMI (19-polig)
Steckverbinder B	1 - DVI-D (25-polig)

Umgebungsbedingungen

Betriebstemperatur	-5~+70
Lagertemperatur	-10~+80
Feuchtigkeit	0~70%

Physische Eigenschaften

Farbe	Schwarz
-------	---------

Drahtstärke	28 AWG
Kabellänge	8.0 in [20.3 cm]
Produktlänge	8.0 in [20.3 cm]
Produktbreite	1.6 in [4.0 cm]
Produkthöhe	2.0 in [5.0 cm]
Produktgewicht	1.3 oz [36.0 g]

Verpackungsinformationen

Paketmenge	10
Paketlänge	10.3 in [26.1 cm]
Paketbreite	9.8 in [24.8 cm]
Pakethöhe	1.9 in [4.8 cm]
Versandgewicht (Verpackung)	1.2 lb [0.5 kg]

Verpackungsinhalt

Im Paket enthalten	10 - 8in HDMI® to DVI-D Video Adapter - M/F
--------------------	---

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.