

3ft (1m) Micro HDMI to DVI Cable - Micro HDMI to DVI Adapter Cable - Micro HDMI Type-D Device to DVI-D Single Link Monitor/Display/Projector Video Converter Cord - Durable

**Product ID:** HDDDVIIMM1M



The HDDDVIIMM1M 1m Micro HDMI to DVI-D Cable enables you to view your presentations, videos and pictures saved on your HDMI Micro-equipped mobile devices (Tablet, Smartphone) on a DVI-D capable display or projector. As an option, in order to incorporate audio with your video presentations you can use our 3ft (1m) Slim 3.5mm Stereo Audio Cable (MU3MMS).

Backed by Lifetime Warranty, the HDDDVIIMM1M is designed and constructed for maximum durability, to ensure dependable performance.

## Certifications, Reports and Compatibility



## Applications

- Connect your HDMI Micro-equipped mobile device (Smartphone, Tablet, etc.) to a DVI-D display or projector

## Features

- **MICRO HDMI TO DVI CABLE:** 3.3ft (1m) Micro HDMI male to DVI-D (19-pin) male cable supports Full HD 1920x1200p, 60Hz/1080p video, Single link, 3.9 Gbps bandwidth, 24 Bpp (RGB) color depth
- **DURABLE:** Full HD high speed fully molded video adapter cable with durable PVC jacket for high strength and reliability; Flexible PVC strain relief prevents fraying or damage due to repetitive bending or rough usage; Ideal for

Commercial environments

- **QUALITY CONSTRUCTION:** Micro HDMI to DVI converter cable constructed with 30AWG wire, gold-plated connectors, and superior EMI shielding with Al-Mylar foil and copper braid improve signal integrity and reliability, providing higher quality video and audio
- **APPLICATIONS:** This cord connects Micro HDMI (Type-D) devices: GoPro Hero/Raspberry Pi 4/cameras (DSLR/Video)/Nikon/Canon EOS to your DVI-Digital monitor/DVI display/projector; Ideal for viewing on larger screens; works w/ Samsung/Dell/HP/Acer/LG monitors
- **SPECS:** 3.3 feet (1 meter) ; Black ; HDMI Male (Type-D/Micro) to DVI-Digital (19-pin) Female ; Gold-plated connectors ; 30 AWG ; 0.2" (5mm) OD ; PVC Jacket ; EMI Shield: Al-Mylar foil with 85% Copper Braid

---

**Hardware**

Warranty	Lifetime
Active or Passive Adapter	Passive
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

**Connector(s)**

Connector A	1 - Micro HDMI (19 pin)
Connector B	1 - DVI-D (19 pin)

---

**Physical Characteristics**

Color	Black
Connector Style	Straight
Wire Gauge	30 AWG
Cable Length	3.3 ft [1 m]
Product Length	3.3 ft [1 m]
Product Width	1.6 in [39.5 mm]
Product Height	0.6 in [1.6 cm]
Weight of Product	2.5 oz [71.6 g]

---

**Packaging Information**

Package Quantity	1
Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.4 in [10 mm]
Shipping (Package) Weight	2.9 oz [81.8 g]

---

**What's in the Box**

Included in Package	1 - 1m Micro HDMI to DVI-D Cable - M/M
---------------------	--

---

***\*Product appearance and specifications are subject to change without notice.***