

6ft (2m) HDMI Extension Cable - HDMI Male to Female Cable - 4K HDMI Cable Extender
- 4K 30Hz UHD HDMI Cable with Ethernet M/F - High Speed HDMI 1.4 Cable - HDMI
Cord Extender

Produkt ID: HDEXT2M



This HDMI® extension cable features an HDMI 19-pin (male) connector on one end and an HDMI 19-pin (female) connector on the other, providing an extra connection distance between your HDMI-enabled devices.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Certifikat, rapporter och kompatibilitet



Användning

- Extend your High Speed HDMI® cable by 2-meters, for added flexibility and more convenient A/V device installations

Funktioner

- **HIGH SPEED HDMI EXTENSION CABLE:** 6.6 ft (2 m) HDMI Cable with Ethernet supports 4K (3840x2160p, 24, 25, 30Hz | 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **DURABLE:** Ultra HD high speed fully molded HDMI cable extender with durable PVC jacket for high strength and reliability; Flexible PVC strain relief prevents fraying or damage due to repetitive bending or rough usage; Ideal for Commercial environments
- **KVALITETSKONSTRUKTION:** 30AWG-kabel med guldpläterade kontakter och överlägsen EMI-skärmning med Al-Mylar-folie och kopparfläta (85 % täckning) förbättrar signalintegriteten och tillförlitligheten, ger högre kvalitet på video och ljud
- **APPLICATIONS:** Port extension allows for easier reach (additional 6.6ft/2m) and to protect HDMI ports on your computer/laptop/desktop/workstation; Connect TV/monitor/display/projector; Ideal for home/office and travel; Samsung/Sony/Apple TV/Dell/LG
- **SPECIFIKATIONER:** 2 m | Svart | HDMI 1.4 | HDMI hane till hona | 30 AWG | PVC-mantel | Skärmning: Al-Mylar folie med 85 % flätning | ARC, Deep Color, HDCP 1.4, CEC, YCC601 Color | Stöder HDMI 1.4 och äldre

Hårdvara

Garantipolicy	Lifetime
Kontaktplätering	Guld
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med flätning

Prestanda

Maximal digital upplösning	4K x 2K @ 30 Hz
----------------------------	-----------------

Kontakt(er)

Connector A	1 - HDMI (19-stifts)
Connector B	1 - HDMI (19-stifts)

Utseende

Färg	Svart
Tråddimension	30 AWG
Kabellängd	6.6 ft [2 m]

Produktlängd	6.6 ft [2.0 m]
Produktbredd	0.9 in [2.2 cm]
Produkthöjd	0.5 in [1.3 cm]
Produktvikt	4.2 oz [120.0 g]

Förpackning

Förpackningsantal	1
Paketets längd	6.3 in [16.0 cm]
Paketets bredd	5.0 in [12.6 cm]
Paketets höjd	1.3 in [3.4 cm]
Fraktvikt (förpackning)	4.0 oz [112.0 g]

Vad det är i lådan

Ingår i paketet	1 - 2 m HDMI Extension Cable - M/F
-----------------	------------------------------------

Warranty Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.