

2m (6ft) HDMI Extension Cable - HDMI Male to Female Cable - 4K HDMI Cable Extender - 4K 30Hz UHD HDMI Cable with Ethernet M/F - High Speed HDMI 1.4 Cable - HDMI Cord Extender

Product ID: HDEXT2M



The HDEXT2M HDMI extension cable (2m) features an HDMI 19-pin (male) connector on one end and an HDMI 19-pin (female) connector on the other, providing an extra 2-meter connection distance between your HDMI-enabled devices.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

Guaranteed for dependable performance, this high quality extension cable is backed by StarTech.com's Lifetime Warranty.

About StarTech.com HDMI to HDMI Cables:

StarTech.com High Speed HDMI extension cables are expertly designed and constructed of only top quality materials to ensure high quality, high-definition performance. The HDMI standard combines high bandwidth video and multi-channel digital audio into a single cable, and provides crystal clear image resolution.

Certifications, Reports and Compatibility



Applications

- Extend your High Speed HDMI cable by 2-meters, for added flexibility and more convenient A/V device installations

Features

- **HIGH SPEED HDMI EXTENSION CABLE:** 6.6 ft (2 m) HDMI Cable with Ethernet supports 4K (3840x2160p, 24, 25, 30Hz 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **DURABLE:** Ultra HD high speed fully molded HDMI cable extender with durable PVC jacket for high strength and reliability; Flexible PVC strain relief prevents fraying or damage due to repetitive bending or rough usage; Ideal for Commercial environments
- **QUALITY CONSTRUCTION:** 30AWG wire with gold-plated connectors, and superior EMI shielding with Al-Mylar foil and copper braid (85% coverage) improve signal integrity and reliability, providing higher quality video and audio
- **APPLICATIONS:** Port extension allows for easier reach (additional 6.6ft/2m) and to protect HDMI ports on your computer/laptop/desktop/workstation; Connect TV/monitor/display/projector; Ideal for home/office and travel; Samsung/Sony/Apple TV/Dell/LG
- **SPECS:** 6.6 ft (2 m) Black HDMI 1.4 HDMI Male to Female 30 AWG PVC Jacket Shield: Al-Mylar foil with 85% Braid ARC, Deep Color, HDCP 1.4, CEC, YCC601 Color Supports HDMI 1.4 and earlier

Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Physical Characteristics

Color	Black
Wire Gauge	30 AWG
Cable Length	6.6 ft [2 m]
Product Length	6.6 ft [2.0 m]

Product Width	0.9 in [2.2 cm]
Product Height	0.5 in [1.3 cm]
Weight of Product	4.2 oz [120.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	1.0 in [2.6 cm]
Shipping (Package) Weight	5.4 oz [152.0 g]

What's in the Box

Included in Package	1 - 2 m HDMI Extension Cable - M/F
---------------------	------------------------------------

****Product appearance and specifications are subject to change without notice.***