

3ft (91cm) Mini HDMI to HDMI Cable with Ethernet - 4K 30Hz High Speed Slim Mini HDMI to HDMI Adapter Cable - Mini HDMI Type-C Device to HDMI Monitor/Display - Video Converter Cord

Product ID: HDMIACMM3S



This Slim High Speed HDMI Mini to HDMI Cable with Ethernet is designed to connect devices that feature an HDMI Mini port to an HDMI-enabled display/device, providing a cost-saving solution for connecting cutting-edge and next-generation HDMI-enabled devices to existing HDMI technology.

High Speed HDMI

This HDMI 1.4b cable supports Ultra HD 4K resolutions (3840x2160p at 30Hz, or 4096x2160p at 24Hz), and a bandwidth of 10.2 Gbps for seamless video and audio transmission. It also supports wide aspect ratios, making it perfect for both home entertainment systems and professional presentations. With support for 3D video and 8-channel audio (5.1/7.1/Dolby Digital Plus/Dolby TrueHD), you can enjoy a fully immersive viewing and listening experience.

Constructed with 36 AWG copper wire, gold-plated connectors, and superior EMI shielding using Al-Mylar foil and a copper braid, this cable minimizes signal loss and interference. This ensures clear, high-quality audio and video transmission with exceptional reliability.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Certifications, Reports and Compatibility



Applications

- Designed for use with mobile devices and cellular phones that are equipped with an HDMI Mini port
- A single cable solution for quickly connecting your HDMI Mini-equipped digital camera to your TV

Features

- **HIGH SPEED MINI HDMI TO HDMI CABLE:** 3 ft Mini HDMI 1.4b Cable with Ethernet supports 4K (3840x2160p, 24, 25, 30Hz 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **SLIM AND DURABLE:** Ultra HD slim (0.14"/3.6mm OD) & light weight Mini HDMI to HDMI adapter cable with flexible strain relief prevents damage due to repetitive bending; Slim cable design reduces bend radius, improving flexibility for Commercial applications
- **QUALITY CONSTRUCTION:** Mini HDMI to HDMI converter cable constructed w/ 36AWG wire, gold-plated connectors, and superior EMI shielding with Al-Mylar foil and copper braid improve signal integrity and reliability, providing higher quality video and audio
- **APPLICATIONS:** This slim cord connects Mini HDMI (Type-C) devices such as phones, tablets, laptops and cameras (DSLR/Video) to your HDMI (Type-A) TV/monitor/display/projector; Ideal for viewing on larger screens; Samsung/Sony/Apple TV/Dell/LG
- **SPECS:** 3 foot Black HDMI 1.4b HDMI Male (HDMI Type-C/Mini) to HDMI Male (Type-A/Standard) 36 AWG PVC Jacket Shield: Al-Mylar foil with Braid ARC, Deep Color, HDCP 1.4, CEC YCC601 Color Supports HDMI 2.0 & earlier Lifetime Warranty

Hardware

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - Mini HDMI (19 pin)

Physical Characteristics

Color	Black
-------	-------

Connector Style	Straight
Wire Gauge	36 AWG
Cable Length	3.0 ft [0.9 m]
Cable OD	0.1 in [3.4 mm]
Product Length	36.0 in [91.4 cm]
Product Width	0.4 in [1.0 cm]
Product Height	0.8 in [2.0 cm]
Weight of Product	0.9 oz [25.0 g]

Packaging Information

Package Quantity	1
Package Length	5.1 in [12.9 cm]
Package Width	5.0 in [12.7 cm]
Package Height	0.7 in [1.9 cm]
Shipping (Package) Weight	1.1 oz [32.0 g]

What's in the Box

Included in Package	1 - 3 ft Slim High Speed HDMI Cable with Ethernet - HDMI to HDMI Mini M/M
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***