

6ft Micro HDMI to HDMI Cable with Ethernet - 4K 30Hz Video - Durable High Speed Micro HDMI Type-D to HDMI 1.4 Adapter Cable/Converter Cord - UHD HDMI Monitors/TVs/Displays

Product ID: HDMIADMM6



The HDMIADMM6 6-foot High Speed HDMI to HDMI Micro cable enables you to connect devices with an HDMI Micro port to a display/device with a standard HDMI port - a cost-saving solution for connecting cutting-edge and next-generation HDMI-capable devices to existing HDMI technology.

The HDMI/HDMI Micro cable features high-quality gold-tipped connectors that ensure peak connectivity, and is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- A single-cable solution for quickly connecting your Smartphone or portable device to your HDMI-enabled TV or display

Features

- **HIGH SPEED MICRO HDMI TO HDMI CABLE:** 6ft HDMI 1.4b adapter cable with Ethernet supports 4K (3840x2160p, 24, 25, 30Hz 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **DURABLE:** Ultra HD high speed fully molded Micro HDMI to HDMI converter cable w/ durable PVC jacket for high strength/reliability; Flexible PVC strain relief prevents fraying or damage due to repetitive bending/rough usage
- **QUALITY CONSTRUCTION:** Micro HDMI to HDMI cord constructed with 34AWG wire & gold-plated connectors, and superior EMI shielding with Al-Mylar foil and copper braid improve signal integrity and reliability, providing higher quality video and audio

- **APPLICATIONS:** This adapter cable connects Micro HDMI (Type-D) devices: GoPro Hero/Raspberry Pi 4/cameras (DSLR/Video)/Nikon/Canon EOS to your HDMI (Type-A monitor/display/projector; Ideal for viewing on larger screens; Samsung/Sony/Apple TV/Asus ZenBook

- **SPECS:** 6ft Black HDMI 1.4b HDMI Male (Type-D/Micro) to HDMI Male (Type-A/Standard) 34 AWG PVC Jacket Shield: Al-Mylar foil with Braid ARC, Deep Color, HDCP 1.4, CEC YCC601 Color Supports HDMI 1.4 and earlier Lifetime Warranty

Hardware

Warranty	Lifetime
Number of Conductors	19
Cable Jacket Material	PVC - Polyvinyl Chloride

Connector(s)

Connector A	HDMI (19 pin)
Connector B	Micro HDMI (19 pin)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	34 AWG
Cable Length	6.0 ft [1.8 m]
Cable OD	0.2 in [4.2 mm]
Product Length	6.0 ft [1.8 m]
Weight of Product	2.2 oz [62 g]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.5 in [12 mm]
Shipping (Package) Weight	2.4 oz [67 g]



What's in the Box

Included in Package	6 ft High Speed HDMI Cable with Ethernet - HDMI to HDMI Micro M/M
---------------------	--

****Product appearance and specifications are subject to change without notice.***

