

15ft (4.6m) HDMI® to DVI-D Cable - M/M

Produkt-ID: HDMIDVIMM15



The HDMIDVIMM15 15-foot HDMI® to DVI-D cable enables you to connect a DVI-D video card (or other DVI-D output device) to a display that incorporates HDMI technology; the cable supports bi-directional operation that also allows the reverse configuration, delivering digital video from an HDMI-enabled output to a DVI-D capable display.

A valuable addition to any digital signage, multimedia or home theater application, this high performance cable is designed to provide the best quality picture available through either HDMI technology or DVI digital connections.

This durably constructed HDMI-DVI-D cable is backed by StarTech.com's Lifetime Warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Compatible with HDMI®/DVI-capable LCD TVs, LCD Projectors, Plasma TVs, HDTVs, DVD Players and set-top boxes
- Connecting a DVI-D output device (video card, etc.) to an HDMI®-enabled monitor/display
- Connecting an HDMI-capable output device (video card, etc.) to a DVI-D monitor/display

Merkmale

- 1x HDMI male connector
- 1x DVI-D male connector
- Molded connectors with strain relief
- High quality construction

Hardware

Garantiebestimmungen	Lifetime
Active or Passive Adapter	Passiv
Steckverbinderplatten	Nickel

Steckverbinder

Steckverbinder A	1 - HDMI (19-polig)
Steckverbinder B	1 - DVI-D (19-polig)

Umgebungsbedingungen

Betriebstemperatur	-10°C to 80°C (14°F to 176°F)
Lagertemperatur	-20°C to 80°C (-4°F to 176°F)
Feuchtigkeit	30% ~ 80%

Physische Eigenschaften

Farbe	Schwarz
Drahtstärke	28 AWG
Kabellänge	14.7 ft [4.5 m]
Produktlänge	15.1 ft [4.6 m]
Produktbreite	1.5 in [3.7 cm]
Produkthöhe	0.6 in [1.6 cm]

Produktgewicht 10.9 oz [308.0 g]

Verpackungsinformationen

Paketmenge 1

Paketlänge 15.6 in [39.5 cm]

Paketbreite 5.2 in [13.3 cm]

Pakethöhe 0.9 in [2.2 cm]

Versandgewicht (Verpackung) 11.0 oz [312.0 g]

Verpackungsinhalt

Im Paket enthalten 1 - 15 ft HDMI® to DVI-D Cable - M/M

Garantieinformationen

Warranty Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.