

6ft Mini HDMI to HDMI Cable with Ethernet - 4K 30Hz High Speed Mini HDMI to HDMI Adapter Cable - Mini HDMI Type-C Device to HDMI Monitor/Display - Durable Video Converter Cord

Product ID: HDMIACMM6



The HDMIACMM6 6-foot HDMI to HDMI Mini cable lets you connect devices with an HDMI Mini (type-C) port to a display/device with an HDMI (standard, type-A) port - a cost-saving solution for connecting cutting-edge and next-generation HDMI-enabled devices to existing HDMI technology.

The HDMI/HDMI Mini cable features high-quality, gold-tipped connectors that ensure peak connectivity, and is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- A single-cable solution for quickly connecting your HDMI-capable A/V devices
- Features a high-quality, gold tipped cable that will optimize the performance of your digital camera or camcorder.

Features

- **HIGH SPEED MINI HDMI TO HDMI CABLE:** 6 ft Mini HDMI 1.4b Cable with Ethernet supports 4K (3840x2160p, 24, 25, 30Hz 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video

- **DURABLE:** Ultra HD high speed fully molded Mini HDMI To HDMI adapter cable with durable PVC jacket for high strength and reliability; Flexible PVC strain relief prevents fraying or damage due to repetitive bending; Ideal for Commercial environments
- **QUALITY CONSTRUCTION:** Mini HDMI to HDMI converter cable constructed w/ 30AWG wire, gold-plated connectors, and superior EMI shielding with Al-Mylar foil and copper braid improve signal integrity and reliability, providing higher quality video and audio
- **APPLICATIONS:** This short cord connects Mini HDMI (Type-C) devices such as phones, tablets, laptops and cameras (DSLR/Video) to your HDMI (Type-A) TV/monitor/display/projector; Ideal for viewing on larger screens; Samsung/Sony/Apple TV/Dell/LG
- **SPECS:** 6 foot Black HDMI 1.4b HDMI Male (HDMI Type-C/Mini) to HDMI Male (Type-A/Standard) 30 AWG PVC Jacket Shield: Al-Mylar foil with Braid ARC, Deep Color, HDCP 1.4, CEC YCC601 Color Supports HDMI 1.4 and earlier Lifetime Warranty

Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Data Transfer Rate	10 Gbps
Maximum Digital Resolutions	4K x 2K @ 30 Hz

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - Mini HDMI (19 pin)

Physical Characteristics

Color	Black
Wire Gauge	30 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	0.8 in [21.0 mm]

Product Height	0.5 in [1.2 cm]
Weight of Product	3.6 oz [101.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.1 in [2.0 mm]
Shipping (Package) Weight	3.7 oz [106.0 g]

What's in the Box

Included in Package	1 - 6 ft High Speed HDMI Cable with Ethernet- HDMI to HDMI Mini- M/M
---------------------	--

****Product appearance and specifications are subject to change without notice.***