

3m HDMI naar DVI-D kabel - M/M

Productcode: HDMIDVIMM10



The HDMIDVIMM10 10-foot HDMI® to DVI-D cable enables you to connect a DVI-D video card (or other DVI-D output device) to a display that incorporates HDMI technology; the cable supports bi-directional operation that also allows the reverse configuration, delivering digital video from an HDMI-enabled output to a DVI-D capable display.

A valuable addition to any digital signage, multimedia or home theater application, this high performance cable is designed to provide the best quality picture available through either HDMI technology or DVI digital connections.

This durably constructed HDMI-DVI-D cable is backed by StarTech.com's Lifetime Warranty.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Compatible with HDMI®/DVI-capable LCD TVs, LCD Projectors, Plasma TVs, HDTVs, DVD Players and set-top boxes
- Connecting a DVI-D output device (video card, etc.) to an HDMI®-enabled monitor/display
- Connecting an HDMI-capable output device (video card, etc.) to a DVI-D monitor/display

Eigenschappen

- 1 HDMI mannelijke connector
- 1 DVI-D mannelijke connector
- Gegoten connectoren met trekontlasting
- Hoogwaardige constructie

Hardware

Garantiebeleid	Lifetime
Active or Passive Adapter	Passief
Connectormateriaal	Nikkel
Type kabelmantel	PVC - Polyvinyl Chloride
Kabelafscherming	Aluminium-Mylar folie met vlechtwerk

Connector(en)

Connector A	1 - HDMI (19-polig)
Connector B	1 - DVI-D (19-polig)

Fysieke eigenschappen

Kleur	Zwart
Draaddikte	28 AWG
Kabellengte	10.0 ft [3.0 m]
Lengte product	10.0 ft [3.0 m]
Breedte product	1.6 in [4.0 cm]
Hoogte product	0.4 in [1.0 cm]
Gewicht product	7.5 oz [212.0 g]

Verpakkingsinformatie

Verpakkingsaantal	1
Lengte Verpakking	5.4 in [13.6 cm]
Package Width	15.0 in [38.2 cm]
Package Height	1.3 in [3.2 cm]
Verzendgewicht (verpakt)	8.3 oz [234.0 g]

Wat wordt er
meegeleverd

Meegeleverd	1 - 10 ft HDMI® to DVI-D Cable - M/M
-------------	--------------------------------------

Garantiebepalinge
n

Warranty	Levenslang
----------	------------

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.