

10 ft High Speed HDMI Cable with Ethernet - Ultra HD 4k x 2k HDMI Cable - HDMI to HDMI M/M

Product ID: HDMIMM10HS



The HDMIMM10HS 10-foot High Speed HDMI Cable with Ethernet supports the advanced capabilities of the High-Definition Multimedia Interface, including Ethernet data inter-connectivity with compatible HDMI-enabled products, and is fully backward compatible with older HDMI-capable devices.

The cable features gold-plated HDMI (male) connectors which help to ensure a high quality digital connection capable of transmitting high-definition video and multi-channel audio between devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, stereo receivers and more.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

All StarTech.com High Speed HDMI Cables are expertly designed and constructed of top quality materials to deliver dependable high-definition performance, and are backed by Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Quick-connect single HDMI cable replaces multiple audio and video cables, reducing clutter and hassle
- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVRs, etc.
- Connecting HDMI-equipped devices such as DVD players, game consoles, etc.
- Enables multiple devices to share an Internet connection (where applicable, device must support High Speed HDMI with Ethernet)

Features

- Gold-plated HDMI connectors
- High quality construction
- 3D and Ethernet ready (for supported devices)
- Supports Ultra HD Resolutions up to 4k x 2k

Hardware

Warranty	Lifetime
Number of Conductors	2
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	HDMI (19 pin)
Connector B	HDMI (19 pin)

Environmental

Operating Temperature	0C to 35C (32F to 95F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	5%-80% RH (no condensation)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	10.0 ft [3.0 m]
Cable OD	0.3 in [7.3 mm]



Product Length	10.0 ft [3.0 m]
Product Width	0.8 in [20.2 mm]
Product Height	0.4 in [10.3 mm]
Weight of Product	8.3 oz [235.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	1.2 in [30.0 mm]
Shipping (Package) Weight	8.6 oz [243.0 g]

What's in the Box

Included in Package	10ft High Speed HDMI Cable with Ethernet - HDMI - M/M
---------------------	---

****Product appearance and specifications are subject to change without notice.***

