15ft (4.6m) Flat High Speed HDMI Cable with Ethernet - Ultra HD 4k x 2k HDMI Cable - HDMI to HDMI M/M

Product ID: HDMIMM15FL

This Flat High Speed HDMI Cable with Ethernet supports the advanced capabilities of the High Definition Multimedia Interface, including Ethernet data interconnectivity with compatible HDMI devices. The cable features a flat-shaft design that makes it the ideal solution for in-wall installations or installation under carpet or along baseboard.

This HDMI 1.4b cable supports Ultra HD 4K resolutions (3840x2160p at 30Hz), and a bandwidth of 10.2 Gbps for seamless video and audio transmission. It also supports wide aspect ratios, making it perfect for both home entertainment systems and professional presentations. With support for 3D video and 8-channel audio (5.1/7.1/Dolby Digital Plus/Dolby TrueHD), you can enjoy a fully immersive viewing and listening experience.

Constructed with 28 AWG copper wire, gold-plated connectors, and shielding using Al-Mylar foil and a copper braid, this cable minimizes signal loss and interference. This ensures clear, high-quality audio and video transmission with exceptional reliability.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Certifications, Reports and Compatibility

Applications

• Connect HDMI-equipped devices like LCD TVs, LCD Projectors, Plasma TVs, HDTVs and DVD Players

• Connect multiple devices with one Internet connection (satellite receivers, DVD players, A/V receivers, High

Definition TVs, game consoles and more)

• This quick-connect, single HDMI cable can replace multiple audio and video cables, reducing clutter and hassle, while the flat wire design allows convenient installation under carpets or behind walls

Features

• 3D and Ethernet ready for supported devices

• Supports IP-based applications

• Supports Ultra HD Resolutions up to 4k x 2k

• Supports High Speed HDMI

• Gold-plated HDMI connectors

General		
	UPC	065030842174
	Package Quantity	1
	Warranty	Lifetime
Physical & Environmental		
	Color	Black
	Connector Style	Straight
	Wire Gauge	28 AWG
	Cable Length	15.0 ft [4.6 m]
	Cable OD	0.2 in [4 mm]
	Product Length	15.0 ft [4.6 m]
	Product Width	0.9 in [23.5 mm]
	Product Height	0.4 in [10.8 mm]
	Weight of Product	15.8 oz [447.0 g]
	Operating Temperature	0C to 35C (32F to 95F)
	Storage Temperature	-10C to 80C (14F to 176F)
	Humidity	5%-80% RH (no condensation)

Performance		
	Maximum Digital Resolutions	4K x 2K @ 30 Hz
Hardware		
	Number of Conductors	19
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
Packaging & In-the-Box		
	Included in Package	1 - 15ft Flat High Speed HDMI Cable with Ethernet - HDMI -M/M
	Package Width	7.7 in [19.5 cm]
	Package Depth	7.7 in [19.6 cm]
	Package Height	1.1 in [28 mm]
	Shipping (Package) Weight	15.9 oz [450 g]
Connector(s)		
	Connector 1 (Quantity)	1
	Connector 1	HDMI
	Connector 2 (Quantity)	1
	Connector 2	HDMI

Product appearance and specifications are subject to change without notice.