

1,8 m High Speed HDMI kabel met Ethernet - Ultra HD 4k x 2k HDMI kabel - HDMI naar HDMI - M/M

Productcode: HDMIMM6HS



The HDMIMM6HS 6-foot High Speed HDMI® Cable with Ethernet supports the advanced capabilities of the High-Definition Multimedia Interface, including Ethernet data inter-connectivity with compatible HDMI-enabled products, and is fully backward compatible with older HDMI-capable devices.

The cable features gold-plated HDMI (male) connectors which help to ensure a high quality digital connection capable of transmitting high-definition video and multi-channel audio between devices such as Blu-Ray Disc™ players, HDTVs, DVD Players, DVRs, stereo receivers and more.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

All StarTech.com High Speed HDMI Cables are expertly designed and constructed of top quality materials to deliver dependable high-definition performance, and are backed by Lifetime Warranty.

## Certificaties, rapporten en compatibiliteit

### Toepassingen

- Quick-connect single HDMI® cable replaces multiple audio and video cables, reducing clutter and hassle
- Connecting high-definition A/V devices such as Blu-Ray Disc™ players, HDTVs, DVRs, etc.
- Connecting HDMI-equipped devices such as DVD players, game consoles, etc.

- Enables multiple devices to share an Internet connection (where applicable, device must support High Speed HDMI® with Ethernet)

## Eigenschappen

- High quality construction
- Gold-plated HDMI® connectors
- 3D and Ethernet ready (for supported devices)
- Supports Ultra HD Resolutions up to 4k x 2k

---

### Hardware

Garantiebeleid	Lifetime
Aantal geleiders	19
Connectormateriaal	Goud
Type kabelmantel	PVC - Polyvinyl Chloride
Kabelafscherming	Aluminium-Mylar folie met vlechtwerk

---

### Prestaties

Maximale digitale resoluties	4K x 2K @ 30 Hz
------------------------------	-----------------

---

### Connector(en)

Connector A	HDMI (19-polig)
Connector B	HDMI (19-polig)

---

### Gebruiksomgeving

Bedrijfstemperatuur	0°C to 35°C (32°F to 95°F)
Opslagtemperatuur	-10°C to 80°C (14°F to 176°F)
Vochtigheid	5%-90% RV (geen condensatie)

---

### Fysieke eigenschappen

Kleur	Zwart
-------	-------



Stijl connector	Recht
Draaddikte	28 AWG
Kabellengte	6.0 ft [1.8 m]
Buitendiameter kabel	0.3 in [7.3 mm]
Lengte product	6.0 ft [1.8 m]
Breedte product	0.8 in [20.2 mm]
Hoogte product	0.4 in [10.3 mm]
Gewicht product	5.2 oz [148.0 g]

---

Verpakkingsinformatie

Verpakkingsaantal	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.0 in [0.1 mm]
Verzendgewicht (verpakt)	5.5 oz [156.0 g]

---

Wat wordt er meegeleverd

Meegeleverd	6 ft High Speed HDMI® Cable with Ethernet - HDMI - M/M
-------------	--

---

\* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.

