

1ft HDMI Splitter Cable, HDMI Male to DVI-D Female Adapter, Full HD 1920x1200p 60Hz, 28AWG, Gold Plated Connectors, HDMI Male to DVI Female Splitter, HDMI Splitter 1 In 2 Out

Product ID: HDMISPL1DH



The HDMISPL1DH 1-foot HDMI to HDMI + DVI-D Splitter Cable splits a Computer or Satellite Receiver's HDMI output signal into one DVI and one HDMI output, allowing you to view content on one DVI display and one HDMI-capable display simultaneously.

Backed by lifetime warranty, our HDMI to HDMI + DVI-D Splitter Cable offers guaranteed durability and reliability.

Certifications, Reports and Compatibility



Applications

- This HDMI splitter cable makes things easy with the capability to instantly connect an HDMI and a DVI-D display to a single digital HDMI-enabled source
- Ideal for use LCD TV, LCD Projectors, Plasma TV, HDTV and DVD Player and set-top box

Features

- **HDMI TO HDMI AND DVI-D SPLITTER:** 1 ft (30 cm) HDMI male to HDMI female and DVI-Digital (24-pin) female splitter supports Full HD 1920x1200p, 60Hz/1080p, Single link, 3.9 Gbps bandwidth, 24 Bpp (RGB) color depth
- **DURABLE:** Full HD high speed fully molded adapter with durable PVC jacket for high strength and reliability;

Flexible strain relief prevents fraying or damage due to repetitive bending or rough usage; Ideal for Commercial environments

- **QUALITY CONSTRUCTION:** 28AWG wire with gold-plated connectors, and superior EMI shielding with Aluminium foil improve signal integrity and reliability, providing higher quality video and audio
- **APPLICATIONS:** Connect two monitors/DVI displays/projectors with HDMI and DVI-Digital connectors from single HDMI source; use existing HDMI M/M or DVI-D M/M cable; for home offices/boardrooms/conference rooms/classrooms; Samsung/Dell/HP/Acer/LG monitors
- **SPECS:** 1 ft (30 cm) Black HDMI Male to HDMI female and DVI-Digital (24-pin) Female Gold-plated connectors 28 AWG 0.25" (6.5mm) Outer Diameter PVC Jacket EMI Shield: Aluminium foil

Performance

Warranty	Lifetime
Maximum Digital Resolutions	1920 1200 @ 60Hz

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - DVI-D (25 pin)
	1 - HDMI (19 pin)

Special Notes / Requirements

Note	This product will split your video signal to deliver two identical images of the same resolution. It cannot be used to span an image across two displays, or to show different images on each display.
------	--

Physical Characteristics

Color	Black
Cable Length	1.0 ft [0.3 m]
Product Length	12.0 in [30.5 cm]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	3.9 oz [111.0 g]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	1.5 in [3.8 cm]
Shipping (Package) Weight	4.1 oz [116.0 g]

What's in the Box

Included in Package	1 - 1 ft HDMI Splitter Cable - HDMI to HDMI and DVI-D - M/F
---------------------	---

****Product appearance and specifications are subject to change without notice.***