

6 ft 180 Rotating High Speed HDMI Cable - HDMI - M/M

**Product ID:** HDMIROTMM6



The HDMIROTMM6 High Speed HDMI Swivel Cable (6 ft) features two gold plated 180 flexible HDMI connectors, which provide a direct link between HDMI-enabled devices such as Blu-Ray players, HDTVs, DVD Players, stereo receivers and more.

The swiveling/pivoting HDMI connectors offer the ability to adjust your installations in tight/narrow spaces where standard connectors will not fit (e.g. wall-mounted flat panel televisions), without having to bend the cable at sharp angles.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

The HDMIROTMM6 6-foot HDMI cable is backed by StarTech.com's Lifetime Warranty.

About StarTech.com HDMI to HDMI Cables:

StarTech.com High Speed HDMI digital video and audio cables are expertly designed and constructed of only top quality materials to ensure high quality, high definition performance. The HDMI standard combines high bandwidth video and multi-channel digital audio into a single cable, and provides crystal clear image resolution.

## Certifications, Reports and Compatibility

### Applications

- Connecting your HDMI-capable TV or Monitor to an audio-video source which incorporates HDMI technology
- Connecting to an HDMI-enabled A/V source with very little space near the connection point

## Features

- Two 180 HDMI Swivel/Pivot connectors
- Supports High Speed HDMI device connections
- Gold-plated HDMI connectors
- Supports resolutions up to 4k x 2k

---

### Hardware

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)

---

### Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

---

### Connector(s)

Connector A	HDMI (19 pin)
Connector B	HDMI (19 pin)

---

### Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]
Cable OD	0.3 in [7.3 mm]
Product Length	6.0 ft [1.8 m]
Weight of Product	4.3 oz [123 g]

---

### Packaging



**Information**

Package Length	4.3 in [10.9 cm]
Package Width	0.8 in [20 mm]
Package Height	8.3 in [21 cm]
Shipping (Package) Weight	4.4 oz [124 g]

---

**What's in the Box**

Included in Package	6 ft 180 Rotating High Speed HDMI Cable - HDMI - M/M
---------------------	--

---

***\*Product appearance and specifications are subject to change without notice.***

