

15m (50 ft) Active CL2 In-wall High Speed HDMI Cable - Ultra HD 4k x 2k HDMI Cable - HDMI to HDMI - M/M

Product ID: HDMM15MA



The HDMM15MA 50 ft Active High Speed HDMI Cable features a built-in active signal booster for a connection distance of up to 50 feet (15m) between your HDMI-enabled devices, with no signal loss.

This durable yet lightweight cable features thinner HDMI wire construction that allows for a more flexible installation with minimal clutter. Plus, the cable features built-in amplifier circuitry which actively boosts the HDMI signal with no external power required.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

This 15 meter HDMI cable is backed by StarTech.com's 2-year Warranty.

Please Note: This cable features unidirectional architecture which requires that the cable is installed in the correct direction. Please refer to the "source" and "display" labels on the HDMI connectors in order to ensure that the device and the HDMI source are connected properly.

Certifications, Reports and Compatibility

Applications

- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc., over long distances, with no signal loss

Features

- Built-in, active amplifier circuitry
- Supports Ultra HD Resolutions up to 4k x 2k
- Provides connection distances up to 50 feet away
- Gold-plated HDMI connectors
- High quality construction

Prominence

Warranty	2 Years
Description CDW 75 - 1st Line	StarTech.com 50ft 15m Active High Speed Long HDMI 1.4 Cable CL2 In-wall 4K

Hardware

Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CL2 Rated
Chipset ID	Redmere - PRE1692

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	HDMI (19 pin)
Connector B	HDMI (19 pin)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	26 AWG (0.404 mm)
Cable Length	49.2 ft [15 m]
Cable OD	0.3 in [7.5 mm]



Product Length	49.2 ft [15 m]
Weight of Product	33.3 oz [943 g]

Packaging Information

Package Quantity	1
Package Length	13.0 in [33 cm]
Package Width	10.0 in [25.5 cm]
Package Height	2.3 in [58 mm]
Shipping (Package) Weight	33.9 oz [960 g]

What's in the Box

Included in Package	15m Active High Speed HDMI Cable - HDMI - M/M
---------------------	---

****Product appearance and specifications are subject to change without notice.***

