

20ft (6m) High Speed HDMI Cable – Ultra HD 4k x 2k HDMI Cable – HDMI to HDMI M/M

Produkt-ID: HDMM20



This High Speed HDMI™ Cable with Ethernet is designed to deliver superior video and audio performance while ensuring reliable connectivity with a variety of HDMI devices, including HDTVs, stereo receivers, projectors, gaming consoles, and more.

High Speed HDMI™

This HDMI 1.4b cable supports Ultra HD 4K resolutions (3840x2160p at 30Hz, or 4096x2160p at 24Hz), Full HD (1920x1080p at up to 120Hz), and a bandwidth of 10.2 Gbps for seamless video and audio transmission. It also supports wide aspect ratios, making it perfect for both home entertainment systems and professional presentations. With support for 3D video and 8-channel audio (5.1/7.1/Dolby Digital Plus/Dolby TrueHD), you can enjoy a fully immersive viewing and listening experience.

Premium Build Quality

Constructed with 24 AWG copper wire, gold-plated connectors, and superior EMI shielding using Al-Mylar foil and a copper braid, this cable minimizes signal loss and interference. This ensures clear, high-quality audio and video transmission with exceptional reliability.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Connecting high-definition A/V devices such as Blu-Ray Disc™ players, HDTVs, DVD Players, DVRs, game consoles, projectors etc.

Merkmale

- 2x HDMI® Male Connectors
- Gold-plated HDMI connectors
- High quality construction
- Supports Ultra HD Resolutions up to 4k x 2k

Hardware

Garantiebestimmungen	Lifetime
Steckverbinderplatten	Gold
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Typ der Kabelabschirmung	Aluminium-Mylar-Folie mit Geflecht

Leistung

Max. Digitalauflösungen	4K x 2K @ 30 Hz
-------------------------	-----------------

Steckverbinder

Steckverbinder A	1 - HDMI (19-polig)
Steckverbinder B	1 - HDMI (19-polig)

Physische Eigenschaften

Farbe	Schwarz
Steckverbinderart	Gerade
Drahtstärke	24 AWG
Kabellänge	20.0 ft [6.1 m]

Außendurchmesser des Kabels 0.4 in [10 mm]

Produktlänge 20.0 ft [6.1 m]

Produktbreite 0.8 in [2.0 cm]

Produkthöhe 0.4 in [1.1 cm]

Produktgewicht 1.1 lb [0.5 kg]

Verpackungsinformationen

Paketmenge 1

Paketlänge 9.5 in [24.1 cm]

Paketbreite 9.8 in [24.9 cm]

Pakethöhe 2.1 in [5.3 cm]

Versandgewicht (Verpackung) 1.5 lb [0.7 kg]

Verpackungsinhalt

Im Paket enthalten 1 - 20 ft High Speed HDMI® Cable - HDMI - M/M

Garantieinformationen

Warranty Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.