

## 3m High Speed HDMI Cable - Ultra HD 4k x 2k HDMI Cable - HDMI to HDMI M/M

Product ID: HDMM3M



The HDMM3M High Speed HDMI cable (3m/9.8ft) features 2 gold-plated HDMI (male) connectors and durable high quality construction to provide a dependable HDMI to HDMI connection between devices such as Blu-Ray Disc players, HDTVs, DVD Players, stereo receivers, projectors and more.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

The HDMM3M 3-meter/9.8ft HDMI cable is backed by StarTech.com's Lifetime Warranty.

StarTech.com High Speed HDMI digital video and audio cables are expertly designed and constructed of only top quality materials to ensure high quality, high definition performance. The HDMI standard combines high bandwidth video and multi-channel digital audio into a single cable, and provides crystal clear image resolution.

This is a replacement product for StarTech.com's 10 ft High Speed HDMI Cable - HDMI- M/M (HDMIMM10).

### Certifications, Reports and Compatibility



### Applications

- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc.
- A convenient, single-cable solution for connecting high-definition set-top boxes, A/V receivers

### Features

- Gold-plated HDMI connectors
- High quality construction
- 2x HDMI Male Connectors
- Supports Ultra HD Resolutions up to 4k x 2k

<b>Hardware</b>	Warranty	2 Years
	Connector Plating	Gold
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
<b>Performance</b>	Maximum Digital Resolutions	4K x 2K @ 30 Hz
<b>Connector(s)</b>	Connector A	HDMI (19 pin)
	Connector B	HDMI (19 pin)
<b>Environmental</b>	Operating Temperature	0C to 50C (32F to 122F)
	Storage Temperature	-20C to 70C (-4F to 158F)
	Humidity	60% at 25C
<b>Physical Characteristics</b>	Color	Black
	Connector Style	Straight
	Wire Gauge	28 AWG
	Cable Length	9.8 ft [3 m]
	Product Length	9.8 ft [3.0 m]
	Product Width	0.8 in [20.800 mm]
	Product Height	0.4 in [10.800 mm]
	Weight of Product	7.1 oz [202.000 g]
<b>Packaging Information</b>	Package Quantity	1
	Package Length	15.6 in [4.0 cm]
	Package Width	5.4 in [1.4 cm]
	Package Height	0.9 in [24.000 mm]
	Shipping (Package) Weight	7.3 oz [207.000 g]
<b>What's in the</b>	Included in Package	3m High Speed HDMI Cable - HDMI - M/M

**Box**

---

*\*Product appearance and specifications are subject to change without notice.*

