

2m Left Angle High Speed HDMI Cable - Ultra HD 4k x 2k HDMI Cable - HDMI to HDMI M/M

Product ID: HDMM2ML



The HDMM2ML High Speed HDMI cable (2m/6.5ft) features an HDMI male connector on one end and a left-angled connector on the other, for a dependable connection between HDMI-enabled devices even with limited space around a device's HDMI port. The left-angled HDMI connector allows the shaft of the cable to fit neatly against a device's HDMI port, in such a way as to minimize the space required near the connection point, which helps make installation easier in narrow spaces and reduces strain on the connection.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

The HDMM2ML 2-meter/6.5ft angled HDMI cable is backed by StarTech.com's Lifetime Warranty.

About StarTech.com HDMI to HDMI Cables:

StarTech.com High Speed HDMI digital video and audio cables are expertly designed and constructed of only top quality materials to ensure high quality, high definition performance. The HDMI standard combines high bandwidth video and multi-channel digital audio into a single cable, and provides crystal clear image resolution.

Certifications, Reports and Compatibility



Applications

- Connect high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc., in tight installation spaces

Features

- 1x HDMI Male connector
- 1x Left Angle HDMI Male connector
- Supports Ultra HD Resolutions up to 4k x 2k
- Gold-plated molded HDMI connectors
- High quality construction

Hardware

| | |
|-----------------------|--------------------------------|
| Warranty | Lifetime |
| Connector Plating | Gold |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |

Performance

| | |
|-----------------------------|-----------------|
| Maximum Digital Resolutions | 4K x 2K @ 30 Hz |
|-----------------------------|-----------------|

Connector(s)

| | |
|-------------|-------------------|
| Connector A | 1 - HDMI (19 pin) |
| Connector B | 1 - HDMI (19 pin) |

Physical Characteristics

| | |
|-------------------|------------------|
| Color | Black |
| Wire Gauge | 28 AWG |
| Cable Length | 6.6 ft [2 m] |
| Product Length | 6.6 ft [2.0 m] |
| Product Width | 0.0 in [0.0 mm] |
| Product Height | 0.0 in [0.0 cm] |
| Weight of Product | 4.6 oz [130.0 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Quantity | 1 |
| Package Length | 8.9 in [22.5 cm] |
| Package Width | 4.9 in [12.5 cm] |
| Package Height | 1.1 in [28.0 mm] |
| Shipping (Package) Weight | 4.8 oz [135.0 g] |

What's in the Box

| | |
|---------------------|---|
| Included in Package | 1 - 2m Left Angled High Speed HDMI Cable - HDMI - M/M |
|---------------------|---|

****Product appearance and specifications are subject to change without notice.***