

10ft (3m) Premium Certified HDMI 2.0 Cable with Ethernet - High Speed Ultra HD 4K 60Hz HDMI Cable HDR10 - HDMI Cord (Male/Male Connectors) - For UHD Monitors, TVs, Displays

Product ID: HDMM3MP



This 3-meter High Speed HDMI cable has been tested in accordance with the Premium HDMI Cable Certification Program. This ensures it's able to deliver the newest technical features that the latest HDMI specifications have to offer, including enhanced resolutions and protection against EMI interference.

Each of our certified Premium High Speed HDMI Cables is labeled with unique anti-counterfeiting authentication, so you can be confident that you have received a genuine certified cable.

The cable supports resolutions of up to 4K@60Hz (3840x2160p) and bandwidths of up to 18Gbps. It also supports HDR (High Dynamic Range) for higher contrast ratio and vivid colors.

With higher resolutions, increased speeds, and sharper images, you can expect an enhanced video experience. The cable is guaranteed to provide the very best HDMI capabilities available today. It's the perfect cable for creating dependable home theater connections or providing lifelike digital signage.

Plus, the cable also supports up to 32 uncompressed digital audio channels to provide crystal-clear sound. The cable is also backward compatible with previous HDMI specifications and will work with all of your existing HDMI devices.

The cable has undergone rigorous compliance testing and is certified by an HDMI Authorized Test Center. This gives you the assurance that the cable will deliver the high-bandwidth enabled features you need. An EMI test is also performed to ensure the cable minimizes interference with wireless signals.

The cable delivers dual video streams so that you can view two videos simultaneously on the same display. Your display must support Multi-View in order to take advantage of dual video streams.

The HDMM3MP is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect 4K/Ultra HD displays and devices

Features

- **HIGH PERFORMANCE:** 9.8ft (3m) Premium Certified HDMI 2.0 Cable with Ethernet, 4K 60Hz (up to 4096x2160p), 18Gbps bandwidth, HDR10 for high contrast ratio, Ultra wide aspect ratio, 32 Ch. multi-stream audio w/1536Hz sampling (5.1/7.1/DD+/Dolby TrueHD/Atmos)
- **DURABLE:** Ultra HD high speed fully molded 4K 60Hz HDMI cable with durable PVC jacket for high strength and reliability; Flexible PVC strain relief prevents fraying or damage due to repetitive bending or rough usage; Ideal for Commercial environments
- **QUALITY CONSTRUCTION:** 30AWG wire with gold-plated connectors, and superior EMI shielding with Al-Mylar foil and copper braid (85% coverage) improve signal integrity and reliability, providing higher quality video and audio
- **APPLICATIONS:** Ideal for home/office and travel, works with computer, laptop, desktop, workstation; UHD HDMI cord to connect your TV, monitor, display or projector; Samsung/Sony/Apple TV/Dell/LG; Compatible with HDMI 2.0 1080p HD and previous HDMI versions
- **SPECS:** 9.8 feet (3 meter) Black HDMI 2.0 Male to Male HDMI cable 30 AWG PVC Jacket Shield: Al-Mylar foil with 85% Braid ARC, Deep Color, HDCP 2.2, CEC, BT.2020 colorimetry Lifetime Warranty

Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Audio Specifications	Up to 32 audio channels with 1536Hz sampling rate
----------------------	---

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Physical

Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	30 AWG
Cable Length	9.8 ft [3 m]
Product Length	9.8 ft [3.0 m]
Product Width	0.8 in [2.0 cm]
Product Height	0.4 in [1.1 cm]
Weight of Product	8.5 oz [240.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	1.0 in [2.5 cm]
Shipping (Package) Weight	8.8 oz [250.0 g]

What's in the Box

Included in Package	1 - 3m Premium High Speed HDMI Cable
---------------------	--------------------------------------

****Product appearance and specifications are subject to change without notice.***