

1ft (30cm) Short High Speed HDMI Cable - Ultra HD 4k x 2k HDMI Cable - HDMI to HDMI M/M

Product ID: HDMM30CM



The HDMM30CM 30cm High Speed HDMI cable enables close-range connections of your HDMI-enabled devices, for situations where a longer cable would create clutter.

Plus, this short HDMI cable provides a portable solution that makes it perfect for carrying as a mobile accessory. When used with an HDMI to Micro or Mini HDMI adapter such as our HDMI 2-in-1 T-adapter, you can connect mobile devices such as your Smartphone, or Tablet to an HD display, or your Digital Camera to a laptop.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

The HDMM30CM 0.3m HDMI cable is backed by StarTech.com's Lifetime Warranty.

About StarTech.com HDMI to HDMI Cables:

StarTech.com High Speed HDMI digital video and audio cables are expertly designed and constructed of only top quality materials to ensure high quality, high-definition performance. The HDMI standard combines high bandwidth video and multi-channel digital audio into a single cable, and provides crystal clear image resolution.

Certifications, Reports and Compatibility



Applications

- Connect HDMI-enabled devices over shorter distances and with reduced clutter

Features

- Offers 30cm in cable length
- Gold-plated HDMI connectors
- High quality construction
- Supports Ultra HD Resolutions up to 4k x 2k

Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	0% to 95% (non-condensing) at 25C (77F)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	1.0 ft [0.3 m]
Product Length	11.8 in [30.0 cm]

Product Width	0.8 in [2.1 cm]
Product Height	0.5 in [1.2 cm]
Weight of Product	1.4 oz [40.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	5.0 in [12.8 cm]
Package Height	0.7 in [1.9 cm]
Shipping (Package) Weight	1.6 oz [44.0 g]

What's in the Box

Included in Package	1 - 0.3m High Speed HDMI Cable - HDMI - M/M
---------------------	---

**Product appearance and specifications are subject to change without notice.*