

5m (15 ft) Active High Speed HDMI Cable - Ultra HD 4k x 2k HDMI Cable - HDMI to HDMI M/M

Product ID: HDMM5MA



The HDMM5MA 15 ft Active High Speed HDMI Cable features a built-in active signal booster for a connection distance of up to 15 feet (5m) between your HDMI-enabled devices, with no signal loss.

This durable, lightweight cable features thinner HDMI wire construction - approximately half the thickness of a regular 5m cable, which allows for a more flexible installation with minimal clutter. Plus, the cable features built-in amplifier circuitry which actively boosts the HDMI signal with no external power required.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

This 5 meter HDMI cable is backed by StarTech.com's 2-year Warranty.

: This cable features unidirectional architecture which requires that the cable is installed in the correct direction. Please refer to the "TV" label on the HDMI connector which plugs into your display, in order to ensure that the device and the HDMI source are connected properly.

Certifications, Reports and Compatibility



Applications

- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc., up to 5m away, with no signal loss

Features

- Thin cable construction – outer diameter (OD) of 3.6mm
- Built-in, active amplifier circuitry
- Gold-plated HDMI connectors
- High quality construction
- Supports Ultra HD Resolutions up to 4k x 2k

Hardware	Warranty	2 Years
	Connector Plating	Gold
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
	Fire Rating	CMG Rated (General Purpose)
	Chipset ID	Redmere - PRA1610
Performance	Maximum Digital Resolutions	4K x 2K @ 30 Hz
Connector(s)	Connector A	HDMI (19 pin)
	Connector B	HDMI (19 pin)
Physical Characteristics	Color	Black
	Connector Style	Straight
	Wire Gauge	36 AWG
	Cable Length	16.4 ft [5 m]
	Cable OD	0.1 in [3.6 mm]
	Product Length	16.4 ft [5.0 m]
	Product Width	0.0 in [0.000 mm]
	Product Height	0.0 in [0.000 mm]
	Weight of Product	3.3 oz [94.000 g]
Packaging Information	Package Quantity	1
	Package Length	8.7 in [2.2 cm]
	Package Width	7.9 in [2.0 cm]
	Package Height	1.0 in [25.000 mm]
	Shipping (Package) Weight	3.6 oz [103.000 g]
What's in the	Included in Package	5m Active High Speed HDMI Cable - HDMI - M/M

Box

**Product appearance and specifications are subject to change without notice.*

