

10-Pack 6ft (1.8m) HDMI Cable, 4K High Speed HDMI Cable w/ Ethernet, UHD 4K 30Hz Video, HDMI 1.4 Cable, Ultra HD HDMI Monitors, Projectors, TVs & Displays, Black HDMI Cord - M/M

Produkt-ID: HDMM610PK



This High Speed HDMI™ Cable with Ethernet is designed to deliver superior video and audio performance while ensuring reliable connectivity with a variety of HDMI devices, including HDTVs, stereo receivers, projectors, gaming consoles, and more.

#### High Speed HDMI™

This HDMI 1.4b cable supports Ultra HD 4K resolutions (3840x2160p at 30Hz, or 4096x2160p at 24Hz), Full HD (1920x1080p at up to 120Hz), and a bandwidth of 10.2 Gbps for seamless video and audio transmission. It also supports wide aspect ratios, making it perfect for both home entertainment systems and professional presentations. With support for 3D video and 8-channel audio (5.1/7.1/Dolby Digital Plus/Dolby TrueHD), you can enjoy a fully immersive viewing and listening experience.

#### Premium Build Quality

Constructed with 30 AWG copper wire, gold-plated connectors, and superior EMI shielding using Al-Mylar foil and a copper braid, this cable minimizes signal loss and interference. This ensures clear, high-quality audio and video transmission with exceptional reliability.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

#### Zertifikate Berichte und Kompatibilität



## Anwendungen

## Merkmale

- **HIGH SPEED HDMI CABLE:** 10 pack 6ft HDMI 1.4b Cable with Ethernet supports 4K video (3840x2160p, 24, 25, 30Hz, 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **DURABLE:** 6ft Ultra HD 4K high speed HDMI cable (fully molded) with durable PVC jacket for high strength and reliability- Flexible PVC strain relief prevents fraying/damage due to repetitive bending or rough usage
- **HOCHWERTIGE KONSTRUKTION:** 28AWG Leiter mit vergoldeten Steckern und eine EMI-Abschirmung mit Al-Mylar-Folie und Kupfergeflecht verbessern die Signalintegrität und zuverlässigkeit und sorgen für eine höhere Video und Audioqualität mit diesem HDMI 1.4 Kabel
- **APPLICATIONS:** Use this 4K HDMI cable in home offices, conference rooms, offices or classrooms; works with your laptop, professional workstation & soundbar for presentations via UHD/4K monitor, projector or large display- Samsung/Sony/Apple TV/Dell/Lenovo
- **SPECS:** 6 foot (1.8 meters)- Black - HDMI 1.4b - HDMI Cord Male to Male - 28 AWG - Gold-plated connectors - Jacket: PVC - Shield: Al-Mylar foil w/ 65% Braid - ARC, Deep Color, HDCP 1.4, CEC - YCC601 Color - Supports HDMI 1.4 and earlier

---

### Hardware

|                          |                                    |
|--------------------------|------------------------------------|
| Garantiebestimmungen     | Lifetime                           |
| Steckverbinderplatten    | Gold                               |
| Typ der Kabelummantelung | PVC - Polyvinyl Chloride           |
| Typ der Kabelabschirmung | Aluminium-Mylar-Folie mit Geflecht |

---

### Leistung

|                         |                 |
|-------------------------|-----------------|
| Max. Digitalauflösungen | 4K x 2K @ 30 Hz |
|-------------------------|-----------------|

---

### Steckverbinder

|                  |                     |
|------------------|---------------------|
| Steckverbinder A | 1 - HDMI (19-polig) |
|------------------|---------------------|

Steckverbinder B 1 - HDMI (19-polig)

---

Umgebungsbedingungen

|                    |                         |
|--------------------|-------------------------|
| Betriebstemperatur | 0 to 80°C (32 to 176°F) |
| Lagertemperatur    | 0 to 80°C (32 to 176°F) |
| Feuchtigkeit       | 0 ~ 95% RH              |

---

Physische Eigenschaften

|                   |                  |
|-------------------|------------------|
| Farbe             | Schwarz          |
| Steckverbinderart | Gerade           |
| Drahtstärke       | 28 AWG           |
| Kabellänge        | 6.0 ft [1.8 m]   |
| Produktlänge      | 6.0 ft [1.8 m]   |
| Produktbreite     | 0.8 in [2.1 cm]  |
| Produkthöhe       | 0.4 in [1.1 cm]  |
| Produktgewicht    | 4.4 oz [126.0 g] |

---

Verpackungsinformationen

|                             |                  |
|-----------------------------|------------------|
| Paketmenge                  | 10               |
| Paketlänge                  | 7.6 in [19.3 cm] |
| Paketbreite                 | 7.1 in [18.1 cm] |
| Pakethöhe                   | 1.1 in [2.9 cm]  |
| Versandgewicht (Verpackung) | 4.6 oz [130.0 g] |

---

Verpackungsinhalt

|                    |                             |
|--------------------|-----------------------------|
| Im Paket enthalten | 10 - High Speed HDMI® Cable |
|--------------------|-----------------------------|

---

Garantieinformatio

nen

Warranty

Lifetime

---

\* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.