

5m (15 ft) Active High Speed HDMI Cable - Ultra HD 4k x 2k HDMI Cable - HDMI to HDMI M/M

Product ID: HDMM5MA



The HDMM5MA 15 ft Active High Speed HDMI Cable features a built-in active signal booster for a connection distance of up to 15 feet (5m) between your HDMI-enabled devices, with no signal loss.

This durable, lightweight cable features thinner HDMI wire construction - approximately half the thickness of a regular 5m cable, which allows for a more flexible installation with minimal clutter. Plus, the cable features built-in amplifier circuitry which actively boosts the HDMI signal with no external power required.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

This 5 meter HDMI cable is backed by StarTech.com's 2-year Warranty.

Please Note: This cable features unidirectional architecture which requires that the cable is installed in the correct direction. Please refer to the "TV" label on the HDMI connector which plugs into your display, in order to ensure that the device and the HDMI source are connected properly.

Certifications, Reports and Compatibility

Applications

- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc., up to 5m away, with no signal loss

Features

- Thin cable construction – outer diameter (OD) of 3.6mm

- Built-in, active amplifier circuitry
- Supports Ultra HD Resolutions up to 4k x 2k
- Gold-plated HDMI connectors
- High quality construction

Prominence

Warranty	2 Years
Description CDW 75 - 1st Line	StarTech.com 15ft 5m Active High Speed HDMI 1.4 Cable Ultra HD 4K x 2K

Hardware

Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Chipset ID	Redmere - PRA1610

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	HDMI (19 pin)
Connector B	HDMI (19 pin)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	36 AWG
Cable Length	16.4 ft [5 m]
Cable OD	0.1 in [3.6 mm]
Product Length	16.4 ft [5.0 m]



Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	3.3 oz [94.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	1.0 in [25.0 mm]
Shipping (Package) Weight	3.6 oz [103.0 g]

What's in the Box

Included in Package	5m Active High Speed HDMI Cable - HDMI - M/M
---------------------	--

****Product appearance and specifications are subject to change without notice.***

