

6ft HDMI Cable - 10 Pack - 4K High Speed HDMI Cable with Ethernet - UHD 4K 30Hz Video - HDMI 1.4 Cable - Ultra HD HDMI Monitors, Projectors, TVs & Displays - Black HDMI Cord - M/M

Product ID: HDMM610PK



The 10-pack High-Speed HDMI 6ft cable features 2 gold-plated HDMI male connectors and durable high-quality construction to provide a dependable HDMI to HDMI connection between devices such as Blu-Ray Disc players, HDTVs, DVD Players, stereo receivers, projectors, and more.

This high-quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high-definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

This product is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility



Applications

Features

- **HIGH SPEED HDMI CABLE:** 10 pack 6ft HDMI 1.4b Cable with Ethernet supports 4K video (3840x2160p, 24, 25, 30Hz, 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **DURABLE:** 6ft Ultra HD 4K high speed HDMI cable (fully molded) with durable PVC jacket for high strength and

reliability- Flexible PVC strain relief prevents fraying/damage due to repetitive bending or rough usage

- **QUALITY CONSTRUCTION:** 28AWG wire with gold-plated connectors, and superior EMI shielding with Al-Mylar foil & copper braid improve signal integrity and reliability, providing higher quality video & audio with this HDMI 1.4 cable
- **APPLICATIONS:** Use this 4K HDMI cable in home offices, conference rooms, offices or classrooms; works with your laptop, professional workstation & soundbar for presentations via UHD/4K monitor, projector or large display-Samsung/Sony/Apple TV/Dell/Lenovo
- **SPECS:** 6 foot (1.8 meters)- Black - HDMI 1.4b - HDMI Cord Male to Male - 28 AWG - Gold-plated connectors - Jacket: PVC - Shield: Al-Mylar foil w/ 65% Braid - ARC, Deep Color, HDCP 1.4, CEC - YCC601 Color - Supports HDMI 1.4 and earlier

Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Environmental

Operating Temperature	0 to 80C (32 to 176F)
Storage Temperature	0 to 80C (32 to 176F)
Humidity	0 ~ 95% RH

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]

Product Length	6.0 ft [1.8 m]
Product Width	0.8 in [2.1 cm]
Product Height	0.4 in [1.1 cm]
Weight of Product	4.4 oz [126.0 g]

Packaging Information

Package Quantity	1
Package Length	18.3 in [46.5 cm]
Package Width	13.8 in [35.0 cm]
Package Height	2.4 in [6.0 cm]
Shipping (Package) Weight	2.9 lb [1.3 kg]

What's in the Box

Included in Package	10 - High Speed HDMI Cable
---------------------	----------------------------

****Product appearance and specifications are subject to change without notice.***