

35 ft 10m Plenum-Rated High Speed HDMI Cable – Ultra HD 4k x 2k HDMI Cable - HDMI to HDMI M/M

Product ID: HDPMM35



The HDPMM35 35 ft plenum-rated High Speed HDMI cable can be installed in air plenums, ducts, walls, conduits, ceilings, or anywhere else a CMP/FT6 fire rating is required.

This cable features 2 gold-plated HDMI (male) connectors and durable construction to provide you with a dependable HDMI to HDMI connection between your A/V devices.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

The HDPMM35 35-foot HDMI cable is backed by StarTech.com's Lifetime Warranty.

About StarTech.com HDMI to HDMI Cables:

StarTech.com High Speed HDMI digital video and audio cables are expertly designed and constructed of only top quality materials to ensure high-quality, high-definition performance. The HDMI standard combines high bandwidth video and multi-channel digital audio into a single cable, and provides crystal clear image resolution.

Certifications, Reports and Compatibility

Applications

- HDMI installations where cable needs to be run through air ducts and plenums, where CMP fire rating is required (educational or commercial installations, etc.)
- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc.

Features

- CMP/FT6 Plenum Fire Rating
- Gold-plated HDMI connectors
- Supports Ultra HD Resolutions up to 4k x 2k

Prominence

Warranty	Lifetime
Description CDW 75 - 1st Line	StarTech.com 35ft Plenum-Rated High Speed Long HDMI 1.4 Cable Ultra HD 4K

Hardware

Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMP Rated (Plenum)

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	HDMI (19 pin)
Connector B	HDMI (19 pin)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	24 AWG
Cable Length	35.0 ft [10.7 m]
Product Length	35.0 ft [10.7 m]
Weight of Product	3.2 lb [1.4 kg]



**Packaging
Information**

Package Quantity	1
Package Length	18.3 in [46.5 cm]
Package Width	13.8 in [35 cm]
Package Height	18.5 in [47.1 cm]
Shipping (Package) Weight	3.3 lb [1.5 kg]

**What's in the
Box**

Included in Package	35 ft Plenum-Rated High Speed HDMI Cable
---------------------	--

****Product appearance and specifications are subject to change without notice.***

