

1m Slim HDMI Cable w/ Low Profile Metal Connectors - 4K High Speed HDMI Cable w/ Ethernet - 4K 30Hz UHD HDMI Cord - 10.2 Gbps - HDMI 1.4 Video / Display Cable 36AWG - HDCP 1.4

Product ID: HDPSMM1M



The HDPSMM1M Pro Series High Speed HDMI cable (1m) features 2 gold-plated HDMI (male) connectors inside a metal connector molding, providing durable, high quality connections with a stylish look that offer the perfect finish for your home theatre or professional A/V environment.

This 1-meter, lightweight HDMI cable also features thinner HDMI wire construction – roughly half the thickness of a regular 1m cable, which allows for a more flexible installation with minimal clutter.

This high-end HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

The HDPSMM1M is backed by StarTech.com's Lifetime Warranty.

About StarTech.com HDMI to HDMI Cables:

StarTech.com High Speed HDMI digital video and audio cables are expertly designed and constructed of only top quality materials to ensure high quality, high definition performance. The HDMI standard combines high bandwidth video and multi-channel digital audio into a single cable, and provides crystal clear image resolution.

Certifications, Reports and Compatibility



Applications

- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc.

Features

- **HIGH SPEED HDMI CABLE:** 3.3 ft (1 m) Slim HDMI Cable with Ethernet supports 4K (3840x2160p, 24, 25, 30Hz 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **SLIM AND DURABLE:** Ultra HD slim (0.14"/3.6mm OD) HDMI cord with durable PVC jacket and strain relief for high strength and reliability; Slim cable design reduces bend radius and improves flexibility; Ideal for Commercial environments
- **QUALITY CONSTRUCTION:** 36AWG wire with gold-plated connectors, and superior EMI shielding with Al-Mylar foil and braid improve signal integrity and reliability, providing higher quality video and audio; Low profile metal connector moldings
- **APPLICATIONS:** Use in home offices/boardrooms/conference rooms/offices/classrooms, works with your laptop/professional workstation/soundbar for presentations via UHD/4K monitors, projector or large display; Samsung/Sony/Apple TV/Dell/Lenovo
- **SPECS:** 3.3 ft (1 m) Black HDMI 1.4b HDMI Cord Male to Male 36 AWG Gold-plated connectors PVC Jacket Shield: Al-Mylar foil with Braid ARC, Deep Color, HDCP 1.4, CEC YCC601 Color Supports HDMI 1.4 and earlier

Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Physical Characteristics

Color	Black
Connector Style	Straight

Wire Gauge	36 AWG
Cable Length	3.3 ft [1 m]
Product Length	39.4 in [100.0 cm]
Product Width	0.0 in [0.0 cm]
Product Height	0.0 in [0.0 cm]
Weight of Product	1.3 oz [37.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.5 in [1.2 cm]
Shipping (Package) Weight	1.7 oz [48.0 g]

What's in the Box

Included in Package	1 - 1m Pro Series Metal High Speed HDMI Cable - HDMI - M/M
---------------------	--

****Product appearance and specifications are subject to change without notice.***