

50ft Hook and Loop Roll - Cut-to-Size Reusable Cable Ties - Bulk Industrial Wire Fastener Tape /Adjustable Fabric Wraps Black / Resuable Self Gripping Cable Management Straps

Product ID: HKLP50



This 50 ft. roll of hook-and-loop cable tie makes it easy to keep your cables neat and tidy by binding them together or binding them to a structure. The self-gripping fabric can be cut to any size and it's 3/4 in. (19 mm) wide which enables a slim wrap-around solution for any computer, appliance or electronics cable, in virtually any environment.

This roll of cable tie offers a quick and easy solution for bundling cables together and securing your cables for better routing. Properly routed cables help protect your equipment, by reducing cable tension and preventing excessive heat caused by unorganized cables restricting airflow.

It uses a hook-and-loop fastening method to ensure a sturdy grip that's easy to apply. With the hook mechanism on one side of the tape and a loop mechanism on the other, you can easily wrap it around your cable bundle, and fasten the cable tie by draping it over itself.

Whether your bundle consists of two small-gauge cables or many large-gauge cables, you can rest assured this roll of cable tie will handle it perfectly. You can cut the hook-and-loop fabric to size using household scissors, meaning you can choose the perfect length for your specific application.

The versatility of the cable tie makes the roll the ideal tool for you to keep on hand in your office, server room or industrial environment. While the most common use for this hook-and-loop fabric is binding and routing cables, you can also use it for other materials in your IT environment such as tools or raceways. The ties are easy to remove, reusable and adjustable, avoiding the hassle and waste of traditional zip ties.

This roll of cable tie is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Keep your office or server room neat and tidy, by binding your equipment cables together
- Prevent damage to your rack-mount equipment by routing cables to improve airflow and reduce port tension

Features

- **VERSATILE USE:** This 50 ft. bulk roll of reusable black hook and loop tape allows you to cut and adjust cable ties to the length you need without the waste of traditional zip ties
- **REDUCE CABLE STRAIN:** This industrial strength hook and loop roll allows you to route cables where needed and relieves strain on connectors that can lead to premature breakage
- **EASY INSTALLATION:** This roll of adjustable fabric hook and loop fastener straps offers a quick and easy solution for fastening cables together and securing your cables
- **PROTECT EQUIPMENT:** Professional cable management using these self-gripping electrical wire hook and loop ties improves airflow around equipment and reduces cable strain
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this hook and loop roll is backed for 2 years, including free lifetime 24/5 multi-lingual technical assistance; Available in different colors for easy visual cable identification

Environmental

Warranty	2 Years
Operating Temperature	14F to 176F (-10C - 80C)
Storage Temperature	14F to 176F (-10C - 80C)

Physical Characteristics

Materials	Nylon
Product Length	50.0 ft [15.2 m]
Product Width	0.7 in [1.9 cm]
Product Height	0.1 in [2.4 mm]
Weight of Product	9.4 oz [266.9 g]

**Packaging
Information**

Package Quantity	1
Package Length	13.0 in [33.0 cm]
Package Width	10.0 in [25.5 cm]
Package Height	0.9 in [2.2 cm]
Shipping (Package) Weight	10.0 oz [283.9 g]

What's in the Box

Included in Package	1 - 50ft Roll of Hook-and-Loop Cable Tie - Black
---------------------	--

****Product appearance and specifications are subject to change without notice.***