

2 Port USB to RS232 Serial DB9 Adapter Cable

Product ID: ICUSB232C2



The StarTech.com ICUSB232C2 2 port USB to DB9 RS232 Serial Adapter Cable lets you connect up to two DB9 RS232 serial devices simultaneously to your Mac or PC laptop or desktop computer through a USB port, as though the computer offered an onboard DB9M connector.

A cost-effective solution that bridges the compatibility gap between modern computers and legacy serial peripherals.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Perfect for IT Administrators looking to add legacy functionality to newer notebooks, PCs and servers that lack an integrated RS232 port
- Connect, monitor and control industrial/automotive sensors and equipment
- Connect bar code scanners, receipt printers and other point of sale devices
- Connect a satellite receiver, serial modem, or PDA with serial sync
- Connect and program LED and Digital signage boards with serial communication ports

Features

- Fully compliant with USB 1.1 specifications

- Easy Plug-and-Play installation
- Bus powered, no external power adapter required
- USB to 2 Port Straight-Through RS232 Serial Adapter

Hardware

Warranty	2 Years
Ports	2
Interface	Serial
Bus Type	USB 2.0
Port Style	Cable Adapters
Chipset ID	Prolific - PL2303HXA Prolific - PL2303RA

Performance

Maximum Data Transfer Rate	230Kbps
Serial Protocol	RS-232
FIFO	192 Bytes

Connector(s)

Connector Type(s)	USB Type-A (4 pin) USB 2.0 DB-9 (9 pin, D-Sub)
-------------------	---

Software

OS Compatibility	Windows 8-10 is only supported by RevB Windows CE 4.2, 5.2, 98SE, ME, 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server 2003, 2008 R2, 2012, 2016, 2019 macOS 10.6 to 10.14, 11.0 Linux 2.4.x to 4.11.x <i>LTS Versions only</i>
------------------	--

Special Notes / Requirements

System and Cable Requirements	1 USB 1.1 (or above) port
-------------------------------	---------------------------



Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-20C to 80C (-4F to 176F)
Humidity	0~65% RH

Physical Characteristics

Color	Black
Material	Plastic
Cable Length	12.2 in [31 cm]
Product Length	12.2 in [31 cm]
Weight of Product	4.8 oz [137 g]

Packaging Information

Package Length	4.1 in [10.4 cm]
Package Width	1.6 in [41 mm]
Package Height	8.5 in [21.5 cm]
Shipping (Package) Weight	4.8 oz [137 g]

What's in the Box

Included in Package	2 Port USB to RS232 Serial Cable
---------------------	----------------------------------

****Product appearance and specifications are subject to change without notice.***

