

USB-C to Parallel Printer Cable

Product ID: ICUSBCPLLD25



This USB-C to parallel printer cable allows you to connect your USB-C enabled laptop or desktop computer to a DB25 printer.

Cost-saving solution

A cost-effective and reliable solution, the USB to DB25 adapter saves you the expense of replacing a parallel printer for the sake of USB compatibility. It turns an available USB-C port on your laptop or desktop computer into a DB25 female parallel port, allowing you to connect a DB25 printer to your computer as if the necessary parallel port was built-in.

Easy installation and portability

The printer cable is supported by a broad range of operating systems, including Windows, Linux, and macOS, which makes it easy to integrate into mixed OS environments. It supports plug-and-play installation, saving you time and hassle.

The printer cable is USB powered, so there's no need for an external power adapter.

The ICUSBCPLLD25 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility





Applications

- Enables you to quickly add a parallel port to your USB-C enabled laptop or computer, for use with printers with DB25 connectors
- Ideal solution for notebooks or desktop computers lacking a parallel port

Features

- Connect your USB-C enabled laptop or desktop computer to a DB25 printer
- Compatible with Windows, Linux, and macOS
- Turns an available USB-C port on your laptop or desktop computer into a DB25 Female parallel port
- Easy plug-and-play installation

Hardware

Warranty	2 Years
Ports	1
Interface	Parallel
Bus Type	USB-C
Chipset ID	Prolific - PL2305

Performance

Maximum Data Transfer Rate	1.5Mbps
----------------------------	---------

Connector(s)

Connector Type(s)	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)
	1 - DB-25 (25 pin, D-Sub)

Software

OS Compatibility	Windows 7, 8.1, 10, 11
	Windows Server 2008 R2, 2012 R2, 2016, 2019
	macOS 10.11 and 10.15, 11.0, 12.0, 13.0, 14.0, 15.0
	Linux 2.6.x to 4.4x LTS Versions only

Special Notes / Requirements

System and Cable Requirements	One available USB-C port
-------------------------------	--------------------------

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	5C to 40C (41F to 140F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	0~80% RH non-condensing

Physical Characteristics

Color	Black
Product Length	6.1 ft [1.8 m]
Product Width	0.0 in [0.0 cm]
Product Height	0.0 in [0.0 cm]
Weight of Product	3.2 oz [92.0 g]

Packaging Information

Package Quantity	1
Package Length	6.1 in [15.4 cm]
Package Width	5.9 in [15.1 cm]
Package Height	1.1 in [2.8 cm]
Shipping (Package) Weight	3.8 oz [108.0 g]

What's in the Box

Included in Package	1 - parallel printer adapter cable
	1 - quick-start guide

****Product appearance and specifications are subject to change without notice.***