

Professional RJ45 Network Cable Tester with 4 Remote Loopback Plugs

ID del Producto: LANTESTPRO



StarTech.com's Advanced Network Cable Tester (RJ45) lets you test several long network cables faster and more efficiently than ever before.

The network cable tester uses remote loop-back plugs, each with their own unique, easy-to-identify ID number. If several cables need to be tested, users can put a loop-back plug on the end of each cable run and go to the other end to test and identify each one.

The network cable tester provides a basic continuity test with a pin-map that will identify wiring errors, allowing them to be quickly corrected. The cable tester also identifies several common pinings and displays the applications for each.

Please note: the Network Cable Tester requires a separate 9V battery (not included) to operate.

Certificaciones, Reportes y Compatibilidad



Aplicaciones

- Testing STP and UTP network cables
- Testing in-wall building cabling

Características

- Easy to read LCD display shows continuity, opens, shorts, and pin mismatches.
- A pin mapping of the current cable is displayed while the unit performs the test.
- Identifies (8) different wiring schemes plus (1) temporary user-defined scheme.
- Includes (4) remote locator plugs, each programmed with a unique ID number so multiple drops can be tested before moving the plugs to new outlets.
- Tests both shielded and unshielded cable in local and remote mode.
- Backlit display allows test readings to be visible in dark areas.
- Low battery indicator.
- Canvas carrying case has plenty of extra space for tools, patch cables and remote locator plugs.
- Menu driven user interface makes the tester easy to use and fast for anyone to learn.

Conector(es)

Política de Garantía	2 Years
Tipo(s) de Conector(es)	2 - RJ-45

Indicadores

Indicadores LED	1 - (LCD Display) 2 lines by 16 characters with LED backlight
-----------------	---

Características Físicas

Color	Negro
Longitud del Producto	13.8 in [35.0 cm]
Ancho del Producto	7.5 in [19.0 cm]
Altura del Producto	2.0 in [5.0 cm]
Peso del Producto	11.9 oz [338.0 g]

Información de la Caja

Cantidad de Paquetes	1
----------------------	---

Longitud de la Caja	15.2 in [38.6 cm]
Ancho de la Caja	9.2 in [23.4 cm]
Altura de la Caja	3.6 in [9.2 cm]
Peso (de la Caja) del Envío	2.1 lb [1.0 kg]

Contenido de la Caja

Incluido en la Caja	1 - Remote Cable Tester w. 4 Loopback Plugs
	1 - Instruction sheet

Información Acerca de la Garantía

Warranty	2 Años
----------	--------

* La apariencia y las especificaciones del producto están sujetas a cambios sin previo aviso.