

## 8 Port 10/100 PSE Industrial Power over Ethernet Switch - All 8 Ports PoE

**Product ID:** IES8100POEEU




The IES8100POEEU 8-port 10/100 Mbps Power over Ethernet (PoE) Switch enables you to supply both power and data to up to 8 PoE-capable devices.

The switch complies with 802.3af standards and supplies up to 15.4 W per port - plenty of power for your PoE devices. A flexible solution giving you the freedom to place your equipment in locations where power outlets are not available, this compact PoE Switch features 8 auto-detecting full/half-duplex ports with automatic crossover detection (MDI/MDI-X). A sturdy metal enclosure provides durability in harsh industrial environments.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Power a security camera/network webcam situated in a remote area where power connection is not possible
- Perfect for powering a Wireless Access Point(WAP) in a business environment
- Great for IT administrators implementing PoE supported VoIP phones

- Power your intercom, paging or hallway speaker amplifier
- Enable remote installation of touchscreens or information kiosks
- Retail applications such as RFID readers

## Features

- 8 10/100Mbps Power over Ethernet Ports
- Max. 15.4 W for each PSE/PoE port
- Auto-detect full/half-duplex, MDI/MDI-X
- Store-and-Forward switching
- IEEE 802.3x flow control for full-duplex and back-pressure flow control for half-duplex
- Rugged metal enclosure

### Hardware

|                    |   |
|--------------------|---|
| Warranty           | 2 Years   |
| Ports              | 8   |
| Memory             | 512 K   |
| Industry Standards | IEEE 802.3af, IEEE802.3 10BASE-T, IEEE802.3u<br>100BASE-TX/FX, IEEE802.3x |

### Performance

|                        |   |
|------------------------|---|
| Flow Control           | Half-duplex back-pressure and IEEE802.3x full-duplex flow control |
| Compatible Networks    | 10/100 Mbps   |
| Switching Architecture | Store-and-Forward   |

### Connector(s)

|                |           |
|----------------|-----------|
| External Ports | 8 - RJ-45 |
|----------------|-----------|

### Software

|                  |  |
|------------------|--|
| OS Compatibility | OS Independent; No additional drivers or software required |
|------------------|--|

### Indicators

|                |                    |
|----------------|--------------------|
| LED Indicators | 8 - PoE Act/Status |
|----------------|--------------------|

8 - Link/Act

1 - Power

#### Power

|                              |                           |
|------------------------------|---------------------------|
| Power Source                 | International Power Cords |
| Input Voltage                | 110V-240V AC              |
| Power Consumption (In Watts) | 132                       |

#### Environmental

|                       |                           |
|-----------------------|---------------------------|
| Operating Temperature | 0C to 45C (32F to 113F)   |
| Storage Temperature   | -10C to 70C (14F to 158F) |
| Humidity              | 10~95% RH                 |

#### Physical Characteristics

|                   |                   |
|-------------------|-------------------|
| Color             | Black             |
| Material          | Steel             |
| Product Length    | 6.3 in [16 cm]    |
| Product Width     | 10.5 in [26.6 cm] |
| Product Height    | 1.7 in [4.4 cm]   |
| Weight of Product | 3.1 lb [1.4 kg]   |

#### Packaging Information

|                           |                   |
|---------------------------|-------------------|
| Package Quantity          | 1                 |
| Package Length            | 11.6 in [29.5 cm] |
| Package Width             | 9.4 in [24 cm]    |
| Package Height            | 2.6 in [65.4 mm]  |
| Shipping (Package) Weight | 4.0 lb [1.8 kg]   |

#### What's in the Box

|                     |                        |
|---------------------|------------------------|
| Included in Package | 1 - 8 Port PoE Switch  |
|                     | 1 - Power Cord         |
|                     | 1 - Instruction Manual |

---

**Warranty  
Information**

|          |         |
|----------|---------|
| Warranty | 2 Years |
|----------|---------|

---

***\*Product appearance and specifications are subject to change without notice.***