

3 ft Cat5e Blue Molded Crossover RJ45 UTP Cat5e Patch Cable - 3ft Patch Cord

Productcode: M45CROSS3BL



StarTech.com's Cat5e UTP Crossover Patch Cables offer reliable Ethernet connections. This 3 ft cable meets or exceeds all Category 5e specifications and features a durable blue jacket that simplifies departmental color coding, while providing rugged flexibility for network connections.

To ensure long-lasting performance, our high quality Cat5e UTP Crossover Patch Cables offer PVC molded strain relief that prevents the RJ45 connector termination point from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

StarTech.com's 3 ft Blue Cat5e UTP Crossover Patch Cable is constructed of only top quality materials (100% copper conductors, 24 gauge wire, 50 micron gold connectors) to ensure optimum performance and is backed by StarTech.com's Lifetime Warranty.

Certificaties, rapporten en compatibiliteit

Toepassingen

- Connects workstation to workstation
- Patches from hub to hub

Eigenschappen

- StarTech Category 5e Patch cables are constructed of top quality components
- The Strain relief prevents the cable from being bent at sharp angles at the connector to minimize the

stress at the plug termination point

- Coloured Hoods for departmental colour coding
- StarTech Category 5e patch cables are carefully constructed and tested, to keep the Near End Crosstalk (NEXT) well within acceptable limits

Hardware

| | |
|--------------------|---------------------------------|
| Garantiebeleid | Lifetime |
| Aantal geleiders | 4 pair UTP |
| Type kabelmantel | PVC - Polyvinyl Chloride |
| Brandbestendigheid | CMG goedgekeurd (algemeen doel) |
| Type kabel | Crossover Gegoten |
| Kabelstandaard | TIA/EIA-568-B.1-2001 T568B |

Prestaties

| | |
|-------------------|-----------------|
| Kabelspecificatie | CAT5e - 350 MHz |
|-------------------|-----------------|

Connector(en)

| | |
|-------------|-------|
| Connector A | RJ-45 |
| Connector B | RJ-45 |

Fysieke eigenschappen

| | |
|----------------|-------------------|
| Kleur | Blauw |
| Draaddikte | 24 AWG |
| Type geleider | Gevlochten koper |
| Kabellengte | 36.0 in [91.4 cm] |
| Lengte product | 36.0 in [91.4 cm] |

Verpakkingsinformatie

| | |
|----------------|------------------|
| Package Length | 7.8 in [19.9 cm] |
| Package Width | 0.4 in [10 mm] |



Package Height 8.3 in [21.1 cm]

Verzendgewicht
(verpakt) 1.8 oz [50 g]

Wat wordt er
meegeleverd

Meegleverd 3 FOOT BLUE MOLDED CROSS PATCH CABLE

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.

