

Micro HDMI or HDMI to VGA Adapter - 1920x1200

Product ID: MCHD2VGA



The MCHD2VGA HDMI / Micro HDMI to VGA Converter lets you connect an HDMI-enabled video source device to a VGA monitor or projector. The adapter also includes a Micro HDMI to HDMI adapter, for added compatibility with Micro HDMI tablets and smartphones - an ideal solution for sharing presentations or worksheets from your HDMI and Micro HDMI devices, on a classroom or boardroom projector.

The MCHD2VGA provides an active video connection making the MCHD2VGA the perfect solution for low-power HDMI sources, such as MacBook and Mac Mini computers.

For added convenience, the adapter can be powered using any USB power source, even the computer or television the device is connected to. A power adapter is also included ensuring you can connect the adapter to a regular power outlet where a USB Power source may not be available.

Note: The adapter will not pass digitally encrypted content.

The MCHD2VGA is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Carry with your laptop, smartphone or tablet for BYOD applications with VGA displays
- Share presentations on a classroom or boardroom projector
- Connect the low-powered HDMI port on your Mac Mini or MacBook to a VGA projector
- Power using the USB port on your computer for added mobility and fast installation

Features

- Micro HDMI to HDMI adapter included, for added compatibility with Micro HDMI smartphones and tablets
- Active converter for low-powered HDMI source devices such as MacBook & Mac Mini
- Conveniently USB powered with included A.C outlet to USB adapter
- Supports video resolutions up to 1920 x 1200 / 1080p

Hardware

Warranty	3 Years
Active or Passive Adapter	Active
Ports	1
AV Input	HDMI
AV Output	VGA
Audio	No
Industry Standards	High Speed HDMI

Performance

Supported Resolutions	1920x1200, 1920x1080 (1080p), 1600x1200 @ 60Hz
-----------------------	--

Connector(s)

Connector Type(s)	USB Mini-B (5 pin)
Connector A	HDMI (19 pin)
Connector B	VGA (15 pin, High Density D-Sub)

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Output Voltage	5 DC
Output Current	1 A
Plug Type	USB Mini-B (5 pin)
Power Consumption (In	1.75



Watts)

Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-20C to 70C (-4F to 158F)

Physical Characteristics

Color	Black
Material	Plastic
Product Length	2.5 in [64.0 mm]
Product Width	1.6 in [41.0 mm]
Product Height	0.6 in [14.0 mm]
Weight of Product	1.3 oz [38.0 g]

Packaging Information

Package Length	8.3 in [21.0 cm]
Package Width	5.9 in [15.0 cm]
Package Height	2.0 in [50.0 mm]
Shipping (Package) Weight	10.0 oz [284.0 g]

What's in the Box

Included in Package	HDMI to VGA Adapter
	HDMI to HDMI Micro Cable
	AC to USB Power Adapter (North American)

****Product appearance and specifications are subject to change without notice.***

