

Mini DisplayPort to DVI Adapter - Mini DP to DVI-D Converter - 1080p Video - mDP or Thunderbolt 1/2 Mac/PC to DVI Monitor - Compact mDP 1.2 to DVI Single-Link Adapter Dongle

Product ID: MDP2DVI3



The MDP2DVI3 Mini DisplayPort to DVI Adapter lets you connect your Mini DisplayPort video source (such as any of your MacBook or Microsoft Surface Pro devices with mDP) to a DVI monitor, projector, or display, eliminating the expense of having to upgrade to a Mini DisplayPort-capable monitor.

Compatible with Intel Thunderbolt, when connected directly to a supporting DisplayPort over Thunderbolt I/O port, the adapter supports display or projector resolutions up to 1920x1200 (WUXGA) and is compliant with HDCP standards.

MDP2DVI3 is a passive adapter that requires a DP++ port (DisplayPort++), meaning that DVI and HDMI signals can also be passed through the port.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect your existing DVI monitor to Mini DisplayPort output device
- Ideal for using your DVI monitor as a secondary display

Features

- **MINI DISPLAYPORT TO DVI ADAPTER:** mDP 1.2 (HBR2) to DVI-I (digital only DVI-D) single-link adapter connects a DVI display/projector supporting 1920x1200/1080p 60Hz video; EDID/DDC pass-through ensure compatibility between source & display
- **HOST COMPATIBILITY:** Passive video converter supports mDP++ source including Thunderbolt 1 & 2 MacBooks, MacBook Air & Mac Mini, Microsoft Surface Pro 1-6, desktops (AMD FirePro/NVIDIA Quadro), laptops, mini itx computers, Intel NUC & docks
- **INCREASE PRODUCTIVITY:** Connect a DVI monitor or projector, or add a second display to your workstation using the mDP to DVI adapter dongle. Compact design makes it ideal for travel. 5" (13cm) attached cable
- **SCREW LOCKING DVI:** Mini DisplayPort to DVI display adapter supports DVI screw locking cable to prevent cable from coming loose or accidental disconnection from DVI displays/projectors. Tested with DVI cables up to 25ft. mDP male to DVI female connector
- **EASY TO USE:** With no software or drivers required, the Mini DP to DVI converter works with any OS including Windows, Ubuntu and macOS; Compatible with MiniDP devices like TB1/TB2 MacBooks with Mini DisplayPort

Hardware

Warranty	3 Years
Active or Passive Adapter	Passive
AV Input	Mini DisplayPort - 1.2
AV Output	DVI-I (Digital Only) - Single-Link
Audio	No

Performance

Maximum Digital Resolutions	1920x1200 / 1080p
Wide Screen Supported	Yes
Audio Specifications	DVI - No Audio Support
MTBF	2,205,691 hours

Connector(s)

Connector A	1 - Mini-DisplayPort (20 pin)
Connector B	1 - DVI-I (29 pin)

Special Notes / Requirements

System and Cable Requirements	DP++ (DisplayPort++) port required from video card or video source for DVI and HDMI signal pass-through
-------------------------------	---

Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	0C to 70C (32F to 158F)
Humidity	40%-85%RH

Physical Characteristics

Color	Black
Cable Length	5.1 in [13 cm]
Product Length	7.3 in [18.5 cm]
Product Width	1.6 in [40 mm]
Product Height	0.6 in [1.5 cm]
Weight of Product	0.9 oz [26.5 g]

Packaging Information

Package Quantity	1
Package Length	9.4 in [24 cm]
Package Width	6.3 in [16 cm]
Package Height	0.8 in [20 mm]
Shipping (Package) Weight	1.8 oz [51 g]

What's in the Box

Included in Package	1 - Mini DisplayPort to DVI Adapter
---------------------	-------------------------------------

****Product appearance and specifications are subject to change without notice.***