

Mini DisplayPort to HDMI 4K Audio / Video Converter – mDP 1.2 to HDMI Active Adapter for Mac Book Pro / Mac Book Air – 4K @ 30 Hz - White

Product ID: MDP2HD4KSW



The MDP2HD4KSW Mini DisplayPort to HDMI adapter enables you to connect devices such as the MacBook Pro, MacBook Air and any Microsoft Surface Pro devices with mDP, to an HDMI display. This adapter is compatible with Mini DisplayPort 1.2 & HDMI 4K @ 30 Hz and as a result can support video resolutions up to Ultra HD (4K) as well as the accompanying digital audio up to 7.1 channel surround sound.

With support for Ultra HD (4K) the mDP to HDMI adapter ensures you can convert Mini DisplayPort to HDMI while maintaining an astonishing picture quality fourtimes the resolution of high-definition 1080p. The adapter is also backward compatible with previous DisplayPort revisions 1.0/1.1 with support for resolutions up to 1080p.

For a hassle-free setup the Mini DisplayPort to HDMI adapter allows for plug-and-play installation without any additional software or drivers. Plus, with a small footprint and lightweight design, the adapter maximizes portability.

To ensure compatibility with any Mini DisplayPort output the mDP adapter offers an active conversion. Active video conversion is required to maintain 4K resolutions when converting Mini DisplayPort to HDMI. An active mDP adapter is also ideal for outputting 1080p resolutions by ensuring compatibility with graphics cards that are not capable of outputting multi-mode DP++ signals (e.g. ATI Eyefinity).

To support your Mac the HDMI converter is compatible with Intel Thunderbolt devices that output a DisplayPort video signal.

With a sleek uniform white design the MDP2HD4KSW looks great next to your Mac, and is backed by a 3-year StarTech.com warranty, and lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect your 4K HDMI display to a Mini DisplayPort output port
- Carry with your laptop for BYOD office applications
- Use an HDMI display as a secondary monitor for your Mini DisplayPort computer
- Use your Thunderbolt port to connect your MacBook Pro / MacBook Air to an HDMI Display

Features

- Supports video resolution up to 4K
- Fully compliant with DisplayPort 1.2 revision
- Compatible with Intel Thunderbolt devices that are capable of outputting a DisplayPort signal
- Compact, lightweight design
- Plug-and-play installation
- No power adapter required
- Active Mini DisplayPort conversion
- Supports HDMI 4K @ 30 Hz

Hardware	Warranty	2 Years	
	Active or Passive Adapter	Active	
	AV Input	Mini DisplayPort - 1.2	
	Ports	1	
	AV Output	HDMI - 1.4	
	Audio	Yes	
	Industry Standards	DPCP (DisplayPort Content Protection)	
		HDCP (High Definition Content Protection)	
		DisplayPort 1.2	
		HDMI 1.4	
Performance	Maximum Cable Distance To Display	49.9 ft [15.2 m]	
	Maximum Digital Resolutions	4K x 2K @ 30 Hz	
		4k x 2K (Ultra HD)	
	Supported Resolutions	1920x1200	
	Wide Screen Supported	1920x1080 (1080p)	
	Audio Specifications	1280x720 (720p)	
		Yes	
	HDMI - 7.1 Channel Audio		
Connector(s)	Connector A	Mini-DisplayPort (20 pin)	

Connector B HDMI (19 pin)

Environmental	Operating Temperature	0C to 70C (32F to 158F)
	Storage Temperature	-10C to 80C (14F to 176F)
	Humidity	10%-85%
Physical Characteristics	Color	White
	Cable Length	5.9 in [1.5 cm]
	Product Length	5.9 in [1.5 cm]
	Product Width	0.0 in [0 mm]
	Product Height	0.0 in [0 mm]
	Weight of Product	0.6 oz [16 g]
Packaging Information	Package Length	7.4 in [1.9 cm]
	Package Width	4.1 in [1.0 cm]
	Package Height	0.5 in [13 mm]
	Shipping (Package) Weight	0.8 oz [22 g]
What's in the Box	Included in Package	Mini-DisplayPort to HDMI Active Adapter

**Product appearance and specifications are subject to change without notice.*

