

3 ft Mini DisplayPort to DisplayPort 1.2 Video Cable Adapter M/F - DisplayPort 4k

Produkt ID: MDP2DPMF3



The MDP2DPMF3 3ft Mini DisplayPort™ to DisplayPort 1.2 video cable adapter lets you add a standard DisplayPort connection port to your existing laptop or Mac® Mini. Easy to use and install, this cost-effective solution makes it easy for you to go from Mini DP to DP, in order to get the most from your Mini DisplayPort device.

The Mini DP to DP cable supports high resolutions of up to 4k x 2k (3840 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The MDP2DPMF3 is backed by StarTech.com's Lifetime Warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

Please Note: Newer laptop and desktop computers (e.g. Apple®) come equipped with Thunderbolt™ ports only. Our Mini DP to DP Cables can be connected to the Thunderbolt ports, enabling you to connect your DP compatible displays.

Certifikat, rapporter och kompatibilitet

Användning

- Allows a DisplayPort monitor or display (HP, Dell) to connect to devices that are equipped with a Mini DisplayPort connection
- A Simple way to convert the Mini DisplayPort connector on your laptop into a full-size DisplayPort connector

Funktioner

- High resolution support of up to 4k x 2k
- Support for High Bit Rate 2 (HBR2) bandwidth of up to 21.6 Gbps
- Designed and manufactured to DisplayPort 1.2 standards
- Backward compatible with DisplayPort 1.1
- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP
- Molded Mini DisplayPort connectors with strain relief

Hårdvara

Garantipolicy	Lifetime
Antal ledare	20
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride
Brandteknisk klass	CMG-klass (General Purpose)

Kontakt(er)

Connector A	Mini-DisplayPort (20-stifts)
Connector B	DisplayPort (20-stifts)

Utseende

Färg	Svart
Kontakttyp	Rak
Tråddimension	32 AWG
Kabellängd	36.0 in [91.5 cm]
Yttre kabeldiameter	0.2 in [5 mm]
Produktlängd	36.0 in [91.5 cm]
Produktvikt	1.6 oz [46.3 g]

Förpackning

Förpackningsantal	1
Package Length	4.9 in [12.5 cm]
Package Width	8.7 in [22 cm]
Package Height	0.6 in [15 mm]
Fraktvikt (förpackning)	1.8 oz [51.3 g]

Vad det är i lådan

Ingår i paketet	3 ft Mini DisplayPort to DisplayPort Video Extension Cable - M/F
-----------------	--

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

