

Mini DisplayPort Extension Cable M/F - 6 ft. - 4k

**Product ID:** MDPEXT6



This Mini DisplayPort 1.2 cable lets you extend the connection distance between your Mini DP devices by up to 6 feet.

The cable delivers the ideal solution for better placement of peripheral devices and can be used to connect your Microsoft Surface Pro 4, Surface Book, MacBook, MacBook Pro, MacBook Air, and other mDP enabled devices to Apple's LED Cinema Display or other Mini DisplayPort monitor.

Simply connect your tablet or laptop to the extension cable using a standard Mini DisplayPort Cable and connect the extension cable to your Mini DP monitor.

The cable supports high resolutions of up to 4k x 2k (3840 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The MDPEXT6 is backed by StarTech.com's lifetime warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

Please note: Newer laptop and desktop computers (e.g. Apple) come equipped with Thunderbolt ports only. Our Mini DisplayPort Cables can be connected to the Thunderbolt ports, enabling you to connect your Mini DP compatible displays.

## Certifications, Reports and Compatibility

### Applications

- Extend the connection distance between your Microsoft Surface Pro 4, Surface Book, MacBook, MacBook Pro, MacBook Air, Mac Pro, iMac, or Mac Mini and Apple LED Cinema Display monitor, by 6 feet

## Features

- Provides a clear digital audio video signal
- Guaranteed reliability with our lifetime warranty

---

### Hardware

Warranty	Lifetime
Number of Conductors	20
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)

---

### Connector(s)

Connector A	Mini-DisplayPort (20 pin)
Connector B	Mini-DisplayPort (20 pin)

---

### Physical Characteristics

Color	Black
Connector Style	Latching
Wire Gauge	32 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Weight of Product	2.6 oz [75 g]

---

### Packaging Information

Package Quantity	1
Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.7 in [18 mm]



Shipping (Package) Weight	3.0 oz [84 g]
------------------------------	---------------

---

**What's in the  
Box**

Included in Package	6 ft Mini DisplayPort 1.2 Video Extension Cable - M/F
---------------------	---

---

***\*Product appearance and specifications are subject to change without notice.***

