

6 ft Mini DisplayPort to DVI Cable - M/M

Product ID: MDP2DVIMM6



The MDP2DVIMM6 6-foot Mini DisplayPort to DVI Cable is a cost-effective Mini DisplayPort to DVI link that lets you connect a DVI monitor to a PC or Mac with a Mini DisplayPort output - saving the expense of upgrading the monitor for compatibility. This Mini DisplayPort adapter is the perfect accessory for any of your MacBook or Microsoft Surface Pro devices with mDP. This all-in-one, easy to use Mini DisplayPort/DVI cable requires no additional converters or adapters, and no driver or software installation.

Compatible with Intel Thunderbolt, when connected directly to a supporting DisplayPort over Thunderbolt I/O port.

MDP2DVIMM6 is a passive adapter that requires a DP++ port (DisplayPort++), meaning that DVI and HDMI signals can also be passed through the port.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Keep your existing DVI display with our Mini DisplayPort to DVI video converter cables
- Use a DVI monitor with DisplayPort equipped MacBook's and iMac's with Mini DisplayPort video output

Features

- All-in-one cable design
- Supports resolutions up to 1920x1200 and HDTV resolutions up to 1080p
- No software or additional drivers required

- Compatible with Intel Thunderbolt

Hardware	Warranty	3 Years
	Active or Passive Adapter	Passive
	AV Input	Mini DisplayPort - 1.2
	AV Output	DVI-D - Single-Link
	Audio	No
Performance	Maximum Cable Length	6.0 ft [1.8 m]
	Maximum Digital Resolutions	1920x1200 / 1080p
	Audio Specifications	DVI - No Audio Support
Connector(s)	Connector A	Mini-DisplayPort (20 pin)
	Connector B	DVI-D (25 pin)
Special Notes / Requirements	System and Cable Requirements	DP++ (DisplayPort++) port required on video card or video source for DVI and HDMI signal pass-through.
Environmental	Operating Temperature	0C to 35C (32F to 95F)
	Storage Temperature	-10C to 80C (14F to 176F)
	Humidity	5%-80% RH (no condensation)
Physical Characteristics	Color	Black
	Cable Length	6.0 ft [1.8 m]
	Product Length	6.0 ft [1.8 m]
	Product Width	1.4 in [35.500 mm]
	Product Height	0.7 in [16.800 mm]
	Weight of Product	3.0 oz [84.000 g]
Packaging Information	Package Length	8.7 in [2.2 cm]
	Package Width	7.9 in [2.0 cm]
	Package Height	1.0 in [26.000 mm]
	Shipping (Package) Weight	3.2 oz [92.000 g]
What's in the	Included in Package	6 ft Mini DisplayPort to DVI Cable - M/M

Box

**Product appearance and specifications are subject to change without notice.*

