

10ft (3m) Mini DisplayPort Cable - 4K x 2K Ultra HD Video - Mini DisplayPort 1.2 Cable - Mini DP to Mini DP Cable for Monitor - mDP Cord works w/ Thunderbolt 2 Ports - White

**Product ID:** MDPMM3MW



The MDPMM3MW 3-meter Mini DisplayPort cable (white) features 2 Mini DisplayPort (male) connectors, and offers a dependable solution for connecting any Mini DisplayPort-enabled laptop (including Mac family of products) to a Mini DisplayPort-equipped monitor.

Please note: Newer laptop and desktop computers (e.g. Apple) come equipped with Thunderbolt ports only. Our Mini DisplayPort Cables can be connected to the Thunderbolt ports, enabling you to connect your Mini DP compatible displays.

## Certifications, Reports and Compatibility



## Applications

- Connecting your Mini DisplayPort products to a Mini DisplayPort compatible display

## Features

- **MINI DISPLAYPORT 1.2 CABLE:** This 9.8ft (3m) Mini DisplayPort v1.2 cable supports 4K x 2K video (3840x2400p 60Hz), 21.6 Gbps bandwidth, HBR2, 8Ch Audio, Multi-Stream Transport (MST), GTC for precise audio channel timing & 3D Stereo (2560x1600p 120Hz)
- **COMPATIBILITY NOTE:** This is not a Thunderbolt cable and is not compatible with Thunderbolt peripherals such as

Docking Stations, Displays or External Enclosures; It can however be used to connect a Thunderbolt 2 laptop to a Mini-DisplayPort monitor

- **RELIABLE DESIGN:** Durable ABS connectors with flexible PVC strain relief and jacket prevents fraying or damage due to bending or rough usage; Metal connector sub-structure provides EMI shielding
- **QUALITY CONSTRUCTION:** 30AWG wire with gold-plated connectors for improved signal integrity & reliability; Superior EMI shielding with double sided copper foil provides higher quality video and audio; mDP cable is Backward compatible with DP1.1
- **SPECS:** 9.8ft (3m); White Mini DP Cable; DisplayPort v1.2; mDP Male to mDP Male Cord; 30 AWG; PVC cable jacket, ABS connector shell; Shield: Al-Mylar foil with Braid; Protocols: HBR2, MST, GTC; Backed for Life

---

#### Hardware

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Drain
Fire Rating	CMG Rated (General Purpose)

---

#### Connector(s)

Connector A	1 - Mini-DisplayPort (20 pin)
Connector B	1 - Mini-DisplayPort (20 pin)

---

#### Physical Characteristics

Color	White
Wire Gauge	32 AWG
Cable Length	9.8 ft [3 m]
Product Length	9.8 ft [3.0 m]
Product Width	0.4 in [1.0 cm]
Product Height	0.3 in [8.0 mm]
Weight of Product	3.6 oz [102.0 g]

---

#### Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.8 in [2.0 cm]
Shipping (Package) Weight	3.6 oz [102.0 g]

---

**What's in the Box**

Included in Package	1 - 3 m White Mini DisplayPort Cable - M/M
---------------------	--

---

***\*Product appearance and specifications are subject to change without notice.***