

## Mini DisplayPort to HDMI Converter Cable - 6 ft (2m) - 4K - White

Product ID: MDP2HDMM2MW



This 6-foot Mini DisplayPort to HDMI adapter cable offers a single-cable connection from your mDP equipped Microsoft Surface Pro, MacBook or Ultrabook laptop to an HDMI display or projector. The passive adapter supports video resolutions up to Ultra HD 4K and is Thunderbolt compatible when connected directly to a supporting DisplayPort over Thunderbolt I/O port.

This adapter cable ensures you can maintain an astonishing picture quality, four times the resolution of 1080p, when converting Mini DisplayPort to HDMI.

The adapter is also backward compatible with lower resolution displays and video sources. With support for high-definition resolutions of 1080p and 720p, you can future-proof your existing setup for 4K video.

For the simplest and most discreet installation, this mDP to HDMI adapter connects directly from your Mini DisplayPort video source to the HDMI port on your display. It doesn't need a power source, unlike some converter dongles that require active power and separate video cabling.

At 6ft in length, this adapter cable delivers a compact connection that eliminates excess to ensure a tidy, professional installation. For shorter installations, we also offer a [%product id="MDP2HDMM1MW" text="3 ft mDP to HDMI cable"%] (MDP2HDMM1MW) enabling you to choose the right cable length for your custom installation needs.

The MDP2HDMM2MW is a stylish white adapter that looks great next to your Mac computer, and is backed by a 3-year StarTech.com warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Connect a Mini DisplayPort computer to an HDMI display at your classroom desk or workstation
- Use in your boardroom or office workstations for installations requiring 6 feet of cable
- Install in your home workstation to make your DisplayPort computer compatible with your HDMI display
- Connect your DP video source to a 4K HDMI display

## Features

- Astonishing video quality with support for video resolutions up to 4K at 30 Hz
- Reduce clutter with a 6ft adapter cable
- Avoid the hassle of converters that require additional cabling and power adapters, using this plug-and-play cable adapter
- Supports HDMI 4K at 30 Hz
- Plug-and-play installation
- No power adapter required

<b>Hardware</b>	Warranty	3 Years
	Active or Passive Adapter	Passive
	AV Input	Mini DisplayPort - 1.2
	AV Output	HDMI - 1.4
	Audio	Yes
	Industry Standards	DPCP (DisplayPort Content Protection)
		HDCP (High Definition Content Protection)
DisplayPort 1.2 HDMI 1.4		
<b>Performance</b>	Maximum Digital Resolutions	4K x 2K @ 30 Hz 4k x 2K (Ultra HD)
	Supported Resolutions	1920x1200
	Wide Screen Supported	1920x1080 (1080p)
	Audio Specifications	1280x720 (720p)
	MTBF	Yes
		HDMI - 7.1 Channel Audio
		2,183,131 hours
<b>Connector(s)</b>	Connector A	Mini-DisplayPort (20 pin)
	Connector B	HDMI (19 pin)
<b>Environmental</b>	Operating Temperature	0C to 70C (32F to 158F)

Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10%-85%

---

**Physical Characteristics**

Color	White
Cable Length	6.6 ft [2 m]
Product Length	6.6 ft [2.0 m]
Product Width	1.6 in [41.000 mm]
Product Height	0.6 in [15.000 mm]
Weight of Product	2.7 oz [77.440 g]

---

**Packaging Information**

Package Length	39.4 in [10.0 cm]
Package Width	1.6 in [41.000 mm]
Package Height	0.6 in [15.000 mm]
Shipping (Package) Weight	4.2 oz [120.000 g]

---

**What's in the Box**

Included in Package	mDP to HDMI adapter cable
---------------------	---------------------------

---

*\*Product appearance and specifications are subject to change without notice.*

