

1m 3.5mm 4 Position TRRS Headset Extension Cable - M/F

Product ID: MUHSMF1M



The MUHSMF1M 4-Pole 3.5mm headset extension cable (1m) features a 3.5mm (1/8" TRRS) audio connector on one end and a 3.5mm (1/8" TRRS) audio connector on the other, making it easy to extend the reach between your hands-free headset or headphones, and your iPhone, mobile phone or laptop computer.

To ensure long-lasting performance, this high quality 3.5mm audio extension cable features molded PVC strain relief at each of the 1/8" TRRS connectors, which prevents the cable termination points from bending at sharp angles, in turn reducing the risk of cable damage.

Please note:

To ensure proper hardware detection, we recommend that the external headset be plugged into the adapter first, before the adapter is connected to the computer or mobile device.

Also, in some circumstances, when an extension cable is used with an in-line remote control equipped headset, the remote control functions may not operate properly. This is due to the sensitivity of the remote control circuitry and does not indicate any defect in the cable.

Certifications, Reports and Compatibility



Applications

- Extend the reach between your hands-free headset and an iPhone or other mobile phone
- Add connection distance between your headset and your laptop or desktop computer audio port

Features

- 4-pole 3.5mm connectors with molded PVC strain relief

Hardware

| | |
|-----------------------|--------------------------|
| Warranty | Lifetime |
| Connector Plating | Nickel |
| Cable Jacket Material | PVC - Polyvinyl Chloride |

Connector(s)

| | |
|-------------|-----------------------------------|
| Connector A | 1 - 3.5 mm Mini-Jack (4 Position) |
| Connector B | 1 - 3.5 mm Mini-Jack (4 Position) |

Special Notes / Requirements

| | |
|------|--|
| Note | 3.5 mm Mini-Jack (4 position) male is configured per CTIA Standard |
|------|--|

Physical Characteristics

| | |
|-------------------|--------------------|
| Color | Black |
| Wire Gauge | 28 AWG |
| Cable Length | 3.3 ft [1 m] |
| Product Length | 39.4 in [100.0 cm] |
| Product Width | 0.2 in [0.6 cm] |
| Product Height | 0.2 in [0.6 cm] |
| Weight of Product | 0.7 oz [20.0 g] |

Packaging Information

| | |
|------------------|------------------|
| Package Quantity | 1 |
| Package Length | 8.7 in [22.0 cm] |
| Package Width | 5.0 in [12.8 cm] |
| Package Height | 0.3 in [7.0 mm] |

| | |
|------------------------------|-----------------|
| Shipping (Package) Weight | 0.9 oz [25.0 g] |
|------------------------------|-----------------|

What's in the Box

| | |
|---------------------|---|
| Included in Package | 1 - 1m 3.5mm 4 Position Headset Extension Cable - M/F |
|---------------------|---|

****Product appearance and specifications are subject to change without notice.***