

## 30 ft Coax High Resolution Monitor VGA Cable - HD15 M/M

Produkt ID: MXT101MMHQ30



The MXT101MMHQ30 High Resolution VGA Cable (30ft) is designed to provide the highest video quality possible through VGA, ideally suited for high resolution applications of 1920x1200 and above.

This durably constructed coaxial VGA video cable (HD15 to HD15) eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial VGA cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.

### Certifikat, rapporter och kompatibilitet

#### Användning

- Replace a worn-out or missing VGA monitor cable with this high quality, coax VGA cable
- Supports high resolution VGA monitors (1920x1200)
- Connect a high resolution display to a Desktop PC or video switch, up to 30 feet away

#### Funktioner

- Triple-coaxial + twisted-pair wire for crystal clear display
- Durably constructed cable, with high quality HD15 connectors
- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor

- High quality VGA connectors with molded PVC strain relief

---

#### Hårdvara

Garantipolicy	Lifetime
Antal ledare	14
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med flätning
Brandteknisk klass	CMG-klass (General Purpose)
Antal ferriter	1
Rättsliga godkännanden	UL2919

---

#### Prestanda

Impedans	75 Ohm
----------	--------

---

#### Kontakt(er)

Connector A	VGA (15-stifts, High Density D-Sub)
Connector B	VGA (15-stifts, High Density D-Sub)

---

#### Miljö

Drifttemperatur	0 to 60 °C
Förvaringstemperatur	-20 to 80 °C
Luftfuktighet	0 - 80 %RH

---

#### Utseende

Färg	Svart
Tråddimension	28 AWG
Maximal kontaktdimension	1.3 in [34 mm]
Kabellängd	30.0 ft [9.1 m]



Yttre kabelldiameter	0.4 in [9 mm]
Produktlängd	30.0 ft [9.1 m]
Produktvikt	6.1 oz [173 g]

---

#### Förpackning

Package Length	13.0 in [33 cm]
Package Width	10.0 in [25.5 cm]
Package Height	2.0 in [50 mm]
Fraktvikt (förpackning)	33.3 oz [943 g]

---

#### Vad det är i lådan

Ingår i paketet	30 ft Coax High Resolution Monitor VGA Cable - HD15 M/M
	Nuts

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

