

3 ft Coax High Resolution Monitor VGA Cable - HD15 M/M

Productcode: MXT101MMHQ3



The MXT101MMHQ3 3-foot High Resolution VGA Monitor Cable is designed to provide the highest video quality possible through VGA and is ideally suited for high resolution VGA applications of 1920x1200 and above.

This durably constructed coaxial VGA cable features two HD15 (male) connectors and eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial cables, while providing superior EMI interference protection by using ferrite cores near the connector ends.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Ideal for high resolution monitors (1920x1200 and above)
- Connect any VGA display to a VGA source
- Connect a high resolution display to a Desktop PC or video switch, up to 3 feet away

Eigenschappen

- Triple-coaxial + twisted-pair wire for crystal clear display

- Impedence matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief
- Ferrite core eliminates EMI interference

Hardware

Garantiebeleid	Lifetime
Aantal geleiders	14
Connectormateriaal	Nikkel
Type kabelmantel	PVC - Polyvinyl Chloride
Kabelafscherming	Aluminium-Mylar folie met vlechtwerk
Brandbestendigheid	CMG goedgekeurd (algemeen doel)
Aantal ferrieten	1
Certificaties	UL2919

Prestaties

Impedantie	75 Ohm
------------	--------

Connector(en)

Connector A	1 - VGA (15-polig, D-Sub met hoge dichtheid)
Connector B	1 - VGA (15-polig, D-Sub met hoge dichtheid)

Gebruiksomgeving

Bedrijfstemperatuur	0 to 60 °C
Opslagtemperatuur	-20 to 80 °C
Vochtigheid	0 - 80 %RH

Fysieke eigenschappen

Kleur	Zwart
Draaddikte	28 AWG

Max. afmeting connector	1.3 in [34 mm]
Kabellengte	3.0 ft [0.9 m]
Buitendiameter kabel	0.4 in [9 mm]
Lengte product	36.0 in [91.4 cm]
Breedte product	1.3 in [3.2 cm]
Hoogte product	0.6 in [1.5 cm]
Gewicht product	6.4 oz [180.0 g]

Verpakkingsinformatie

Verpakkingsaantal	1
Lengte Verpakking	8.2 in [20.8 cm]
Package Width	7.6 in [19.2 cm]
Package Height	1.3 in [3.4 cm]
Verzendgewicht (verpakt)	6.6 oz [188.0 g]

Wat wordt er meegeleverd

Meegeleverd	1 - 3 ft Coax High Resolution VGA Monitor Cable - HD15 M/M
	2 - Nuts

Garantiebepalingen

Warranty	Levenslang
----------	------------

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.