

## 25 ft Coax High Resolution Monitor VGA Cable with Audio HD15 M/M

**Product ID:** MXTHQMM25A



The MXTHQMM25A 25-foot High Resolution VGA Monitor Cable with Audio is a high quality SVGA cable designed to provide the highest video quality possible through VGA - a single cable solution, for connecting both video between a VGA video card and monitor, and audio connections between a sound card and external audio device.

StarTech.com's high resolution VGA cable with audio features high quality male-to-male coaxial VGA cable, and is designed to eliminate picture "ghosting" and fuzzy images that are inherent to non-coaxial cables, while providing superior EMI interference protection by using ferrite cores near the connector ends.

The 25-foot SVGA cable (VGA Cable with Audio) is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility

### Applications

- Make video and audio connections using a single cable
- Ideal for high resolution VGA monitors (1920x1200 and above)

### Features

- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief
- Ferrite core eliminates EMI interference

---

**Hardware**

Warranty	Lifetime
Number of Conductors	15
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Number of Ferrites	2
Regulatory Approvals	UL2919

---

**Performance**

Impedance	75 Ohm
-----------	--------

---

**Connector(s)**

Connector A	3.5 mm Mini-Jack (3 Position)
	VGA (15 pin, High Density D-Sub)
Connector B	3.5 mm Mini-Jack (3 Position)
	VGA (15 pin, High Density D-Sub)

---

**Environmental**

Operating Temperature	0 to 60 C
Storage Temperature	-20 to 80 C
Humidity	0 - 80 %RH

---

**Physical Characteristics**

Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	25.0 ft [7.6 m]



Product Length	25.0 ft [7.6 m]
Weight of Product	29.6 oz [839 g]

---

**Packaging Information**

Package Quantity	1
Package Length	12.8 in [32.5 cm]
Package Width	9.8 in [25 cm]
Package Height	1.7 in [44 mm]
Shipping (Package) Weight	30.3 oz [859 g]

---

**What's in the Box**

Included in Package	25 ft Coax High Resolution Monitor VGA Cable with Audio HD15 M/M
---------------------	------------------------------------------------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

