35 ft Coax High Resolution Monitor VGA Cable - HD15 M/M

Product ID: MXT101MMHQ35

The MXT101MMHQ35 High Resolution VGA Cable (35ft) is designed to provide the highest video quality possible through VGA, ideally suited for high resolution applications of 1920x1200 and above.

This durably constructed coaxial VGA video cable (HD15 to HD15) eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial VGA cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.

Certifications, Reports and Compatibility

Applications

• Replace a worn-out or missing VGA monitor cable with this high quality, coax VGA cable

• Supports high resolution VGA monitors (1920x1200)

• Connect a high resolution display to a Desktop PC or video switch, up to 35 feet away

Features

• Triple-coaxial + twisted-pair wire for crystal clear display

• Durably constructed cable, with high quality HD15 connectors

- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor
- High quality VGA connectors with molded PVC strain relief

Hardware		
	Warranty	Lifetime
	Number of Conductors	14
	Connector Plating	Nickel
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
	Fire Rating	CMG Rated (General Purpose)
	Number of Ferrites	1
	Regulatory Approvals	UL2919
Performance		
	Impedance	75 Ohm
Connector(s)		
	Connector A	VGA (15 pin, High Density D-Sub)
	Connector B	VGA (15 pin, High Density D-Sub)
Environmental		
	Operating Temperature	0 to 60 C
	Storage Temperature	-20 to 80 C
	Humidity	0 - 80 %RH
Physical Characteristics		
	Color	Black
	Wire Gauge	28 AWG
	Max Connector Dimension	1.3 in [34 mm]
	Cable Length	35.0 ft [10.7 m]
	Cable OD	0.4 in [9 mm]

	Product Length	35.0 ft [10.7 m]
	Product Width	0.0 in [0.0 cm]
	Product Height	0.0 in [0.0 cm]
	Weight of Product	2.4 lb [1.1 kg]
Packaging Information		
	Package Quantity	1
	Package Length	13.0 in [33.0 cm]
	Package Width	10.0 in [25.5 cm]
	Package Height	2.2 in [5.5 cm]
	Shipping (Package) Weight	2.4 lb [1.1 kg]
What's in the Box		
	Included in Package	1 - 35 ft Coax High Resolution Monitor VGA Cable - HD15 M/M
		2 - Nuts

Product appearance and specifications are subject to change without notice.