

25 ft 7m Plenum-Rated Coax High Resolution Monitor / Projector VGA Cable - HD15 to HD15 M/M

**Product ID:** MXT101PMM25



The MXT101PMM25 25 ft long plenum-rated VGA cable allows for connection distances of up to 25 feet to your monitor or projector and can be installed through air plenums, ducts, walls, conduits, ceilings, or anywhere else a CMP/FT6 fire rating is required.

This durably constructed coaxial cable features two HD15 (male) connectors and eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial cables, while providing superior EMI interference protection by using ferrite cores near the connector ends.

This 25-foot plenum-rated VGA cable is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility

### Applications

- VGA display installations where cable needs to be run through air ducts and plenums, where CMP fire rating is required (educational or commercial installations, etc.)
- Connect a high resolution display to a Desktop PC or video switch, up to 25 feet away

### Features

- CMP/FT6 Plenum Fire Rating
- 2x VGA HD15 male connectors
- Triple coaxial + twisted-pair wire for crystal clear display

- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor
- High quality VGA connectors with molded PVC strain relief
- Supports high resolution VGA monitors (1920x1200 and above)

---

#### Hardware

Warranty	Lifetime
Number of Conductors	14
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMP Rated (Plenum)

---

#### Performance

Impedance	75 Ohm
-----------	--------

---

#### Connector(s)

Connector A	VGA (15 pin, High Density D-Sub)
Connector B	VGA (15 pin, High Density D-Sub)

---

#### Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	25.0 ft [7.6 m]
Product Length	25.0 ft [7.6 m]
Product Width	7.9 in [20.0 cm]
Product Height	0.4 in [10.0 mm]
Weight of Product	24.3 oz [687.0 g]

---

#### Packaging Information

Package Quantity	1
------------------	---

Package Length	18.1 in [46.0 cm]
Package Width	13.8 in [35.0 cm]
Package Height	0.4 in [10.0 mm]
Shipping (Package) Weight	24.5 oz [695.0 g]

---

**What's in the Box**

Included in Package	25ft Plenum-Rated Coax VGA Monitor Cable HDDB15 M/M
---------------------	---

---

*\*Product appearance and specifications are subject to change without notice.*

