

35 ft Coax High Resolution Monitor VGA Cable with Audio HD15 M/M

Product ID: MXTHQMM35A



The MXTHQMM35A 35-foot High Resolution VGA Monitor Cable with Audio is a high quality SVGA cable designed to provide the highest video quality possible through VGA - a single cable solution, for connecting both video between a VGA video card and monitor, and audio connections between a sound card and external audio device.

StarTech.com's high resolution VGA cable with audio features high quality male-to-male coaxial VGA cable, and is designed to eliminate picture "ghosting" and fuzzy images that are inherent to non-coaxial cables, while providing superior EMI interference protection by using ferrite cores near the connector ends.

The 35-foot SVGA cable (VGA Cable with Audio) is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Make VGA video and audio connections using a single, high quality cable

Features

- Ideal for high resolution monitors (1920x1200 and above)
- Ferrite core eliminates EMI interference
- Impedance matched at 75 Ohms for full brightness and vibrant picture color

- Molded connector ends with strain relief
- Triple-coaxial + twisted-pair wire for crystal clear display

Hardware

Warranty	Lifetime
Number of Conductors	15
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Number of Ferrites	2
Regulatory Approvals	UL2919

Performance

Impedance	75 Ohm
-----------	--------

Connector(s)

Connector A	1 - 3.5 mm Mini-Jack (3 Position)
	1 - VGA (15 pin, High Density D-Sub)
Connector B	1 - 3.5 mm Mini-Jack (3 Position)
	1 - VGA (15 pin, High Density D-Sub)

Environmental

Operating Temperature	0 to 60 C
Storage Temperature	-20 to 80 C
Humidity	0 - 80 %RH

Physical Characteristics

Color	Black
Connector Style	Straight

Wire Gauge	28 AWG
Cable Length	35.0 ft [10.7 m]
Product Length	35.0 ft [10.7 m]
Product Width	0.0 in [0.0 cm]
Product Height	0.0 in [0.0 cm]
Weight of Product	2.4 lb [1.1 kg]

Packaging Information

Package Quantity	1
Package Length	8.0 in [20.2 cm]
Package Width	9.1 in [23.0 cm]
Package Height	2.8 in [7.2 cm]
Shipping (Package) Weight	2.5 lb [1.1 kg]

What's in the Box

Included in Package	1 - 35 ft Coax High Resolution Monitor VGA Cable with Audio HD15 M/M
---------------------	--

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***