

20ft (6m) Power Extension Cord, NEMA 5-15R to NEMA 5-15P Black Extension Cord, 13A 125V, 16AWG, Outlet Extension Power Cable, NEMA 5-15R to NEMA 5-15P AC Computer Power Cord - UL Listed

**Product ID:** PAC10120



This 20-foot Computer Power Cord Extension Cable instantly turns a large, awkward power connector into a smaller, streamlined connector.

The power adapter will fit into any socket, maximizing the space on your power strip, surge protector, or wall outlet.

The power adapter also doubles as a power cord extender, giving you an extra 20ft of reach for your monitor, computer case, or any other powered device.

## Certifications, Reports and Compatibility



## Applications

- Extend an existing power cord by an additional 20ft
- StarTech.com's computer power extension cord saves space and conveniently connects large power adapters, so you can maximize all your power/surge strip outlets

## Features

- **POWER EXTENSION CORD:** This 20ft (6m) 16AWG AC power extension cable with NEMA 5-15R and NEMA

5-15P connectors is suitable for workstations/home office Indoor use Rated to carry 125V at 13A

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief on connectors for durability  
Fire Rating: VW-1 3 Conductor extension cord with 100% copper wire This cable is available in other lengths
- **SPECS:** 20ft (6m) AC Power Cord NEMA 5-15R to NEMA 5-15P 16AWG 125V 13A (Max) Jacket Type: SJT  
Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.33in (8.5mm)
- **COMPATIBILITY:** PC Power Extension Cord NEMA 5-15P works with North American outlets Extend a 3-prong power connection from your desktop computer, server, or printer Replacement power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

#### Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

#### Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - NEMA 5-15 Power (North America)

#### Special Notes / Requirements

Note	UL Listed
------	-----------

#### Power

Input Voltage	125 AC
Input Current	13 A

#### Physical Characteristics

Color	Black
Wire Gauge	16 AWG
Cable Length	20.0 ft [6.1 m]
Product Length	20.0 ft [6.1 m]
Product Width	1.0 in [2.5 cm]
Product Height	1.4 in [3.5 cm]

Weight of Product	25.1 oz [711.0 g]
-------------------	-------------------

---

#### Packaging Information

Package Quantity	1
Package Length	9.5 in [24.1 cm]
Package Width	8.5 in [21.7 cm]
Package Height	2.3 in [5.9 cm]
Shipping (Package) Weight	1.6 lb [0.7 kg]

---

#### What's in the Box

Included in Package	1 - 20 ft Power Cord Extension - NEMA 5-15R to NEMA 5-15P
---------------------	---

---

#### Warranty Information

Warranty	Lifetime
----------	----------

---

***\*Product appearance and specifications are subject to change without notice.***