

6ft (2m) Power Extension Cord, NEMA 5-15R to NEMA 5-15P Black Extension Cord, 13A 125V, 16AWG, Outlet Extension Power Cable, NEMA 5-15R to NEMA 5-15P AC Computer Power Cord - UL Listed

Product ID: PAC1016



The PAC1016 power extension cord extends your existing power connection by up to 6ft.

The added cable distance allows you to minimize clutter, giving you more room for additional connections on your power strip, surge protector or wall outlet.

Designed for durability and dependability, this NEMA extension cord is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Extend the connection distance between your PC, Monitor, Laser Printer or Scanner and your power strip, surge protector or wall outlet by up to 6 ft

Features

- **POWER EXTENSION CORD:** This 6ft (2m) 16AWG AC power extension cable with NEMA 5-15R and NEMA 5-15P connectors is suitable for workstations/home office Indoor use Rated to carry 125V at 13A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief on connectors for durability

Fire Rating: VW-1 3 Conductor extension cord with 100% copper wire This cable is available in other lengths

• SPECS: 6ft (2m) AC Power Cord NEMA 5-15R to NEMA 5-15P 16AWG 125V 13A (Max) Jacket Type: SJT Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.33in (8.5mm)

• COMPATIBILITY: PC Power Extension Cord NEMA 5-15P works with North American outlets Extend a 3-prong power connection from your desktop computer, server, or printer Replacement power supply cable/cord

• THE IT PRO'S CHOICE: Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Performance

Maximum Cable Length	6.0 ft [1.8 m]
----------------------	----------------

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - NEMA 5-15 Power (North America)

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	13A

Physical Characteristics

Color	Black
Wire Gauge	16 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]

Weight of Product	8.6 oz [245 g]
-------------------	----------------

Packaging Information

Package Quantity	1
Package Length	4.9 in [12.5 cm]
Package Width	7.8 in [19.8 cm]
Package Height	2.0 in [5.2 cm]
Shipping (Package) Weight	8.8 oz [248.0 g]

What's in the Box

Included in Package	1 - 6ft Power Cord Extension - NEMA 5-15R to NEMA 5-15P
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***